



While-In-Use-Weatherproof Covers

T&B Catalog Number:

CKMUV

UPC Number:

04226900466

Status:

Active

Description:

1-gang Universal While-In-Use Extra-Duty Vertical Receptacle Cover - Silver

Features

| |
|--|
| Die-cast metal construction provides long-lasting durability |
| Combination box or device-mounting design provides flexibility in installation. |
| NEMA 3R rating ensures protection against falling rain, sleet and external ice formation when used with appropriate device boxes |
| Clear UL and CSA markings speed approval by inspectors |
| Wide range of cover depths and receptacle configurations accommodate almost every common plug and cord size when combined with included adapter plates |
| Combination box or device mounting design provides flexibility in installation |

Application

| |
|--|
| Residential-Holiday and landscape lighting, wells and sump pumps, sprinkler systems, plug-in timers, garages and patios |
| Commercial-Vending machines, car washes, outdoor signs, restaurant kitchens, greenhouses and nurseries, marinas, garages and lumberyards |
| Industrial-Manufacturing areas, food processing, water treatment plants, security cameras, laboratories, wash down areas and loading docks |
| Recreational-Pools and spas, parks, playgrounds, zoos, RV connections, athletic fields, ball parks, stadiums, outdoor stages, amphitheaters and golf courses |
| Complies with National Electrical Code Article 406.8 (B) for unattended in use plugs in wet locations. |
| Protects receptacles, switches and plugs for single gang and two gang configurations in dry and wet locations |

General

| | |
|-----------------|-------------------|
| Material | Die Cast Aluminum |
| Finish | Powder-coated |
| Color | Silver |
| Number of Gangs | One |

Dimension Information

| | |
|-----------------------|-------|
| Inside Depth (inches) | 3 1/4 |
|-----------------------|-------|

Packaging

| | |
|--------------------|----------------|
| Package in Units | 6 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 0.84 lbs. Each |

Application Support

| | |
|---|----------------------|
| T&B Sales Drawings | wsd-000492 |
| T&B Instruction Sheets | ta04208-tb2 |
| Product Brochure-Weatherproof While-in-Use Kits | Available on Website |
| D-Pak Merchandising System | Available on Website |
| Industry Cross Reference | Available on Website |

Notes

Less than .004 copper content

Certifications



File Nbr:
E 28688

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com