

## Eaton Classified 3/4" thermal magnetic circuit breaker

**CL115**

**UPC:**786676011549

**Dimensions:**

- **Height:** 3 IN
- **Length:** 3 IN
- **Width:** 1 IN

**Weight:**.3 LB

**Notes:**Replacement for Square D Homeline, GE Type THQ, Crouse-Hinds Type MP, Thomas and Betts Type TB, Murray Type MP, ITE/Siemens Type QP. Requires 1-inch (25.4 mm) space.

**Warranties:**

- Limited lifetime residential, 1 year commercial

**Specifications:**

- **Type:** Type CL 1-Inch classified replacement breaker
- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240 V
- **Main Circuit Breaker:** CL
- **Wire Size:** #14-4 AWG Cu/Al
- **Circuit Breaker Type:** CH
- **Used With:** Square D HOMELINE, General Electric, Crouse-Hinds, Thomas & Betts, Murray and ITE/Siemens Load centers

**Supporting documents:**

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CL115](#)

**Certifications:**

- UL 489

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.

## Eaton Classified 3/4" thermal magnetic circuit breaker

**CL115**

**UPC:**786676011549

**Dimensions:**

- **Height:** 3 IN
- **Length:** 3 IN
- **Width:** 1 IN

**Weight:**.3 LB

**Notes:**Replacement for Square D Homeline, GE Type THQ, Crouse-Hinds Type MP, Thomas and Betts Type TB, Murray Type MP, ITE/Siemens Type QP. Requires 1-inch (25.4 mm) space.

**Warranties:**

- Limited lifetime residential, 1 year commercial

**Specifications:**

- **Type:** Type CL 1-Inch classified replacement breaker
- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240 V
- **Main Circuit Breaker:** CL
- **Wire Size:** #14-4 AWG Cu/Al
- **Circuit Breaker Type:** CH
- **Used With:** Square D HOMELINE, General Electric, Crouse-Hinds, Thomas & Betts, Murray and ITE/Siemens Load centers

**Supporting documents:**

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CL115](#)

**Certifications:**

- UL 489

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.