


CABLE LENGTH METERS

CLM-1000 AND CLM-1000E

TAKE THE GUESSWORK OUT OF CABLE INVENTORY



FAST

- Measures length of cable without removing it from the spool, counting turns or weighing the spool

EASY

- 20 pre-set cable sizes plus 8 user-programmable settings
- Pushbutton selection of Copper or Aluminum cable

VERSATILE

- Measures cable length from 15.0 ft to 100.00 kft
- Measures resistance values down to 199.99 mΩ



USA PHONE 800.435.0786
FAX 800.451.2632

CANADA PHONE 866.384.8813
FAX 800.524.2853

INT'L PHONE +1.815.397.7070
FAX +1.815.397.9247



GREENLEE®

A Textron Company

CABLE LENGTH METERS

CLM-1000 and CLM-1000E

FOR PRODUCT VIDEOS, DEMONSTRATIONS
AND MORE, SCAN THIS QR CODE OR VISIT:

www.youtube.com/GreenleeDEMO



Displays length
in feet or meters

Measures insulated
copper and aluminum
conductors

20 pre-programmed
cable sizes plus eight
user-programable
settings



CLM-1000



FEATURES

- Large, 20,000 count LCD with backlight
- Kelvin-type alligator clips with solid copper contacts assure low-resistance connection to the cable being measured
- Automatic temperature compensation for maximum accuracy and convenience
- Automatic power off to maximize battery life

SPECIFICATIONS

CAT. NO.	WIRE SIZES	LENGTH MEASUREMENT	RESISTANCE MEASUREMENT
CLM-1000	18, 16, 14, 12, 10, 8, 6, 4, 2 AWG; 1/0, 2/0, 3/0, 4/0; 250, 350, 400, 500, 600, 750, 1000 kcmil	15.0 ft to 100.00 kft 5.0 m to 30.00 km (3 Ranges)	199.99 mΩ to 1999.9 Ω (5 Ranges)
CLM-1000E	0.75, 1, 1.5, 2.5, 4, 6, 10, 16, 25, 35, 50, 70, 95, 120, 150, 185, 240, 300, 400, 500 mm ²		

ORDERING INFORMATION

CAT. NO.	UPC NO.	DESCRIPTION
CLM-1000	02719	Cable Length Meter for AWG–kcmil Wire and Cable
CLM-1000E	02720	Cable Length Meter for Metric Wire and Cable
CLM-ROD	02721	Replacement Calibration Rods (2)
CLM-CLIPS	02722	Replacement Kelvin Clips (1 Red, 1 Black)



www.greenlee.com MA6188 05/14

4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070

©2014 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA


Greenlee Textron Inc. is a subsidiary of Textron Inc.



CABLE LENGTH METERS

CLM-1000 AND CLM-1000E

TAKE THE GUESSWORK OUT OF CABLE INVENTORY



FAST

- Measures length of cable without removing it from the spool, counting turns or weighing the spool

EASY

- 20 pre-set cable sizes plus 8 user-programmable settings
- Pushbutton selection of Copper or Aluminum cable

VERSATILE

- Measures cable length from 15.0 ft to 100.00 kft
- Measures resistance values down to 199.99 mΩ



USA PHONE 800.435.0786
FAX 800.451.2632

CANADA PHONE 866.384.8813
FAX 800.524.2853

INT'L PHONE +1.815.397.7070
FAX +1.815.397.9247



GREENLEE®

A Textron Company

CABLE LENGTH METERS

CLM-1000 and CLM-1000E

FOR PRODUCT VIDEOS, DEMONSTRATIONS
AND MORE, SCAN THIS QR CODE OR VISIT:

www.youtube.com/GreenleeDEMO



Displays length
in feet or meters

Measures insulated
copper and aluminum
conductors

20 pre-programmed
cable sizes plus eight
user-programmable
settings



CLM-1000



FEATURES

- Large, 20,000 count LCD with backlight
- Kelvin-type alligator clips with solid copper contacts assure low-resistance connection to the cable being measured
- Automatic temperature compensation for maximum accuracy and convenience
- Automatic power off to maximize battery life

SPECIFICATIONS

CAT. NO.	WIRE SIZES	LENGTH MEASUREMENT	RESISTANCE MEASUREMENT
CLM-1000	18, 16, 14, 12, 10, 8, 6, 4, 2 AWG; 1/0, 2/0, 3/0, 4/0; 250, 350, 400, 500, 600, 750, 1000 kcmil	15.0 ft to 100.00 kft 5.0 m to 30.00 km (3 Ranges)	199.99 mΩ to 1999.9 Ω (5 Ranges)
CLM-1000E	0.75, 1, 1.5, 2.5, 4, 6, 10, 16, 25, 35, 50, 70, 95, 120, 150, 185, 240, 300, 400, 500 mm ²		

ORDERING INFORMATION

CAT. NO.	UPC NO.	DESCRIPTION
CLM-1000	02719	Cable Length Meter for AWG– kcmil Wire and Cable
CLM-1000E	02720	Cable Length Meter for Metric Wire and Cable
CLM-ROD	02721	Replacement Calibration Rods (2)
CLM-CLIPS	02722	Replacement Kelvin Clips (1 Red, 1 Black)



www.greenlee.com MA6188 05/14

4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070

©2014 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA

Greenlee Textron Inc. is a subsidiary of Textron Inc.

