

Eaton CPMV5L-UNV1

Catalog Number: CPMV5L-UNV1

Eaton Crouse-Hinds series Champ CPMV LED wall pack, 0.15A, Cool white, Dimmable driver, 3/4" entry, 100W equiv, 50/60 Hz, Tempered glass lens, 5000 lumens, 116 lm/W, Die cast alum, Yoke mount, 7x6 distribution, 120-277 Vac, 125-250 Vdc, 45W



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Champ CPMV LED wall pack light fixture	CPMV5L-UNV1
	UPC
	662276936249
Product Length/Depth	Product Height
9.16 in	12.76 in
Product Width	Product Weight
12.6 in	14 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 2

Class II, Division 1

Class III

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lamp type

LED

Lumens

5000

Lumens per watt

116

Color temperature

Cool white

Optical distribution

7x6

Mounting Method

Yoke

Voltage rating

120-277 Vac, 125-250 Vdc

Frequency rating

50/60 Hz

Lens material

Tempered glass

Wattage

45W

Amperage Rating

0.15 A

Power factor

> 0.90

Dimming

Dimmable driver

Entry size

3/4"

Material

Die cast aluminum

Equivalent luminaire

100W

Resources

3D models

[SP3D Design Package - Champ CPMV LED Hazardous Area Wallpack Light Fixtures](#)

Brochures

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series CPMV LED brochure](#)

Catalogs

[Crouse-Hinds series Champ CPMV LED catalog page](#)

Certification reports

[Champ CPMV LED Hazardous Area Wallpack Light Fixtures UL certification](#)

[Champ CPMV LED Hazardous Area Wallpack Light Fixtures Canadian certification](#)

Installation instructions

[IF 1892 - Champ-Pak CPMVL LED Wall Pack](#)

Specifications and datasheets

[Eaton Specification Sheet - CPMV5L-UNV1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)