

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2450 NE Inner Loop Building 1 78626-0000, TX Georgetown Phone: 737-444-2615

Fax: 737-444-2617



Height Width

CR20RED Duplex Recp 20A 125V Side Wire RD *Pass & Seymour/Legrand*

Pass & Seymour/Legra	INO
Catalog Number	CR20RED
Manufacturer	Pass & Seymour/Legrand
Description	Commercial Spec Grade Duplex Receptacle, Side Wire 20A 125V
Weight per unit	0.1962 (lbs/each)
Product Category	Con Durnoso Docont & Surgo Dro
Features	
amperage rating	20
connection	Side wire
Dielectric Strength	Withstands 1500V minimum
indoor/outdoor	Indoor
Material	Nylon
Mounting Type	Box
Number of Wires	3
Outlet Type	STRAIGHT BLADE
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 10
Material, Color, and Finish	
Finish	Matte
Dimensions and Weight	
.	0.004

3.281

.780



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2450 NE Inner Loop Building 1 78626-0000, TX Georgetown Phone: 737-444-2615

Fax: 737-444-2617

_						
ı١	2	rri	ın	•	$\boldsymbol{\wedge}$	nc
u	es	GI I	ı	u	UI	113
_					_	

Description	DUPLEX RECP 20A 125V SIDE WIRE RD
extra long description	P&S CR20RED RECEP DUP 20A/125V SIDE
Features	Impact Resistant, Single Piece Plated Steel Mounting Strap
Long Description	Commercial Spec Grade Duplex Receptacle, Side Wire 20A 125V
Product Type	Recep Dup 20A/125V Side Wire Red
Special Features	Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly032 inch thick, brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body. Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for positive conductor containment. Tri-drive termina

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007180145
Manufacturers Part Number	CR20-RED
UPC	785007180145

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Туре	Outlet

Trade Size

Amperage	20.0
,po	<u>-</u> 9.9

Packaging

Carton	1	
Package	100	
Weight Per each	0.1962	

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
Operating Temperature	-40°-60°C
standard	CULUS, UL498, CSA C22.2 No. 42