

# Specifications

## Eaton CS120LA

Eaton commercial grade toggle switch, #14-10 AWG, 20A, Commercial, Flush, 120/277V, Side wire, Screw, Light almond, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Brass, PVC

### General specifications

<b>PRODUCT NAME</b>	Eaton commercial grade toggle switch
<b>CATALOG NUMBER</b>	CS120LA
<b>UPC</b>	032664583179
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	4.2 in
<b>PRODUCT WIDTH</b>	0.902 in
<b>PRODUCT WEIGHT</b>	0.1 lb
<b>CERTIFICATIONS</b>	cULus Listed NOM Federal Specification Classification 6241 05
<b>PRODUCT TYPE</b>	Commercial grade toggle switch



Powering Business Worldwide

## Product specifications

**TYPE** Toggle switch

**AMPERAGE RATING** 20A

**VOLTAGE RATING** 120/277 V

**NUMBER OF POLES** Single-pole

**APPLICATION** Commercial

**WIRING METHOD** Side wire

**SWITCH TYPE** Single-pole

**MOUNTING METHOD** Flush

**CONNECTOR TYPE** Screw

**LOAD TYPE** INC  
MLV  
LED  
ELV  
Fan  
HAL  
CFL  
FLR  
Motor Control

**MATERIAL** PVC

**ALLOWABLE WIRE SIZE** #14-10 AWG

**TERMINAL ENCLOSURE MATERIAL** Brass

**COLOR** Light almond

## Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CS120LA](#)

[Commercial specification grade switches spec sheet](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton CS120LA

Eaton commercial grade toggle switch, #14-10 AWG, 20A, Commercial, Flush, 120/277V, Side wire, Screw, Light almond, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Brass, PVC

### General specifications

<b>PRODUCT NAME</b>	Eaton commercial grade toggle switch
<b>CATALOG NUMBER</b>	CS120LA
<b>UPC</b>	032664583179
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	4.2 in
<b>PRODUCT WIDTH</b>	0.902 in
<b>PRODUCT WEIGHT</b>	0.1 lb
<b>CERTIFICATIONS</b>	cULus Listed NOM Federal Specification Classification 6241 05
<b>PRODUCT TYPE</b>	Commercial grade toggle switch



Powering Business Worldwide

## Product specifications

**TYPE** Toggle switch

**AMPERAGE RATING** 20A

**VOLTAGE RATING** 120/277 V

**NUMBER OF POLES** Single-pole

**APPLICATION** Commercial

**WIRING METHOD** Side wire

**SWITCH TYPE** Single-pole

**MOUNTING METHOD** Flush

**CONNECTOR TYPE** Screw

**LOAD TYPE** INC  
MLV  
LED  
ELV  
Fan  
HAL  
CFL  
FLR  
Motor Control

**MATERIAL** PVC

**ALLOWABLE WIRE SIZE** #14-10 AWG

**TERMINAL ENCLOSURE MATERIAL** Brass

**COLOR** Light almond

## Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CS120LA](#)

[Commercial specification grade switches spec sheet](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2026 Eaton. All Rights Reserved.