



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS15AC1LA 15A 120/277VAC S Wire Comm SP SW La *Pass & Seymour/Legrand*

Catalog Number	CS15AC1LA
Manufacturer	Pass & Seymour/Legrand
Description	Commercial 1-Pole Switch, Side-Wire, 15A 120/277V.
Weight per unit	0.1604 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	TP
actuator	Toggle
amperage rating	15
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
insulation	False
Load Rating	15 A @ 120/277 VAC
Load Type	Universal, Halogen, Xenon, LED, CFL, Incandescent, Fluorescent
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3"
------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	15A SP COMM SW
extra long description	P&S CS15AC1LA 15A 120/277VAC S WIRE
Features	Single Piece Plated Steel Mounting Strap
Long Description	Commercial 1-Pole Switch, Side-Wire, 15A 120/277V.
Product Type	15A 120/277VAC S Wire Comm SP SW La
Special Features	Back & Side wire, locking support, one piece brass alloy contact arm

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007126426
Manufacturers Part Number	CS15AC1-LA
UPC	785007126426

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.1604

Uses, Certifications, and Standards

Application	Commercial/Residential
Mounting	WALL
standard	FEDSPEC, CULUS, UL20, FEDSPEC