

# Specifications

## Eaton CS320B

Eaton commercial grade toggle switch, #14-10 AWG, 20A, Commercial, Wall, 120/277V, Side wire, Screw, Brown, Three-Way, Copper alloy, Terminals: 0.031 in

### General specifications

<b>PRODUCT NAME</b>	Eaton commercial grade toggle switch
<b>CATALOG NUMBER</b>	CS320B
<b>UPC</b>	032664750793
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	4.2 in
<b>PRODUCT WIDTH</b>	0.902 in
<b>PRODUCT WEIGHT</b>	0.15 lb
<b>CERTIFICATIONS</b>	cULus Listed NOM Federal Specification Classification 6241 05
<b>PRODUCT TYPE</b>	Commercial grade toggle switch



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Toggle switch
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	120/277 V
<b>NUMBER OF POLES</b>	Single-pole
<b>APPLICATION</b>	Commercial
<b>WIRING METHOD</b>	Side wire
<b>SWITCH TYPE</b>	Three-way
<b>MOUNTING METHOD</b>	Wall
<b>CONNECTOR TYPE</b>	Screw
<b>MATERIAL</b>	PVC
<b>NUMBER OF WAYS</b>	Three-way
<b>ALLOWABLE WIRE SIZE</b>	#14-10 AWG
<b>TERMINAL ENCLOSURE MATERIAL</b>	Copper alloy
<b>TERMINALS</b>	0.031 in
<b>COLOR</b>	Brown

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CS320B</a>
	<a href="#">Commercial specification grade switches spec sheet</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton CS320B

Eaton commercial grade toggle switch, #14-10 AWG, 20A, Commercial, Wall, 120/277V, Side wire, Screw, Brown, Three-Way, Copper alloy, Terminals: 0.031 in

### General specifications

<b>PRODUCT NAME</b>	Eaton commercial grade toggle switch
<b>CATALOG NUMBER</b>	CS320B
<b>UPC</b>	032664750793
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	4.2 in
<b>PRODUCT WIDTH</b>	0.902 in
<b>PRODUCT WEIGHT</b>	0.15 lb
<b>CERTIFICATIONS</b>	cULus Listed NOM Federal Specification Classification 6241 05
<b>PRODUCT TYPE</b>	Commercial grade toggle switch



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Toggle switch
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	120/277 V
<b>NUMBER OF POLES</b>	Single-pole
<b>APPLICATION</b>	Commercial
<b>WIRING METHOD</b>	Side wire
<b>SWITCH TYPE</b>	Three-way
<b>MOUNTING METHOD</b>	Wall
<b>CONNECTOR TYPE</b>	Screw
<b>MATERIAL</b>	PVC
<b>NUMBER OF WAYS</b>	Three-way
<b>ALLOWABLE WIRE SIZE</b>	#14-10 AWG
<b>TERMINAL ENCLOSURE MATERIAL</b>	Copper alloy
<b>TERMINALS</b>	0.031 in
<b>COLOR</b>	Brown

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CS320B</a>
	<a href="#">Commercial specification grade switches spec sheet</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

