



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street  
72209-0000, AR Little Rock  
Phone: 501-565-1785  
Fax: 501-565-0827



## CS120W 20A 120/277VAC S Wire Comm SP SW WH

*Pass & Seymour/Legrand*

Catalog Number	CS120W
Manufacturer	Pass & Seymour/Legrand
Description	Commercial 1-Pole Switch, Side-Wire, 20A 120/277V.
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	Single pole
actuator	Toggle
amperage rating	20
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Fluorescent, CFL, Halogen, Incandescent, Xenon, Universal, LED
Material	Thermoplastic
media	Yes
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	277 VAC, 120 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	20A 120/277VAC S WIRE COMM SP SW W
extra long description	P&S CS20AC1W 20A 120/277VAC S WIRE
Features	Single Piece Plated Steel Mounting Strap
Long Description	Commercial 1-Pole Switch, Side-Wire, 20A 120/277V.
Product Type	20A 120/277VAC S Wire Comm SP SW W
Special Features	Side wire, locking support, heavy duty toggle



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street  
72209-0000, AR Little Rock  
Phone: 501-565-1785  
Fax: 501-565-0827

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007126471
Manufacturers Part Number	CS20AC1W
UPC	785007126471

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	10
Package	100
Weight Per each	0.15

## Uses, Certifications, and Standards

Application	Commercial
Enclosure	Nylon
Mounting standard	WALL FEDSPEC, CULUS, UL 498/20, FEDSPEC