



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## D2288 Diagonal Cutting Pliers, High-Leverage, 8"

*Klein Tools*

Catalog Number	D2288
Manufacturer	Klein Tools
Description	High Leverage Diagonal-Cutter, Steel Blade Material, 1-3/16 In Cutting Capacity, Plastic Dipped Steel Handle Material, Red (Handle), Plastic Dipped (Handle), 8-1/16 In Overall Length, 13/16 In Jaw Length, 1-3/16 In Jaw Width, 9.6 Oz
Weight per unit	0.6000 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

### Features

Jaw Type	Short
Material	Steel
Process	Induction Hardened

### Material, Color, and Finish

Handle Color	Red
--------------	-----

### Descriptions

Additional Information	Handle Length 6 Inch; Jaw Thickness 13/16 Inch; Handle Finish Plastic Dipped
Commodity Description	PLRS,WRNCH,DRV,SAW,POUCH,TOOL BOX
Description	DIAGONAL CUTTING PLIERS, HIGH-LEVERAGE, 8"
extra long description	HOT RIVETED JOINT, HIGH LEVERAGE, LOCKING JOINT, STANDARD TYPE; STEEL MATERIAL; PLASTIC DIPPED (HANDLE) FINISH; 8.063 INCH OVERALL LENGTH; 0.813 INCH JAW LENGTH; 1.188 INCH JAW WIDTH; CUTTING APPLICATION; FORGED PROCESS; 1.019 INCH CAPACITY; RED HANDLE COLOR; DIAGONAL, SHORT JAW TYPE; HANDLE LENGTH 6 INCH; JAW THICKNESS 0.813 INCH

### Manufacturer Information

GTIN	00092644720406
UPC	092644720406

### Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Hot Riveted Joint, High Leverage

### Packaging

Carton	1
Package	6
Weight Per each	0.6



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....	CUTTING .....
Capacity .....	1-3/16 Inch (Jaw) .....