



TITLE
24
ENERGY SAVER

D703P-W

Convenient, preset dimming control.

Looking for handsome, high-quality dimmers with smooth, extra-convenient operation? Find just what you're looking for in the P&S Harmony™ line.

Harmony Dimmers feature P&S Decorator style — a great match for any décor. You can easily preset your favorite lighting level with the right-side slide control. Then turn lights on and off with the ergonomically designed paddle switch. It's that simple! There's even an LED that lights when the dimmer is off — no fumbling to find the control in the dark.

You'll find even more convenience in P&S Harmony Dimmers: they won't lose their settings if there's a power failure.

Installation's always quick and easy. And with our durable construction, you can count on many years of dependable service. For convenience and value, you can't go wrong with P&S Harmony Dimmers.

Attractive
P&S
Decorator
style

Pass & Seymour



Green LED glows when off —
to make dimmer easy to find
in the dark.

**Sleek, ergonomic P&S
Decorator style** matches
other Decorator devices.

Convenient operation —
combines On/Off Decorator
switch with separate slider
for dimming control.

Constant memory returns lights to
previous level after a power failure.



D703P-W

Cat. No.	Description	Rating
D703P*	Incandescent Single Pole/3-Way	700W
D1103P*	Incandescent Single Pole/3-Way	1100W
DLV703P*	Magnetic Low Voltage Single Pole/3-Way	700VA
DLV1103P*	Magnetic Low Voltage Single Pole/3-Way	1100VA
DFB8P*	120V Two-Wire Fluorescent Single Pole/3-Way	8A
DDH16P*	De-Hummer Fan Speed Control	1.6A

* Color Designation	
I	Ivory
LA	Light Almond
W	White
BK	Black
-	Brown

All devices are UL Listed and CSA Certified.

D703P, D1103P and DDH16P are available in VisionPak™.
Add [V] after the color code.

DFB8P for use with Advance MK10 dimming ballasts.

For additional technical or application-specific information, call
800-223-4185 or visit our website at www.passandseymour.com.
We're eager to put our expertise to work for you.

Distributed by:

USA
P.O. Box 4822
Syracuse, NY 13221-4822
800-611-7277

Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
905-738-9195

Pass & Seymour



TITLE
24
ENERGY SAVER

D703P-W

Convenient, preset dimming control.

Looking for handsome, high-quality dimmers with smooth, extra-convenient operation? Find just what you're looking for in the P&S Harmony™ line.

Harmony Dimmers feature P&S Decorator style — a great match for any décor. You can easily preset your favorite lighting level with the right-side slide control. Then turn lights on and off with the ergonomically designed paddle switch. It's that simple! There's even an LED that lights when the dimmer is off — no fumbling to find the control in the dark.

You'll find even more convenience in P&S Harmony Dimmers: they won't lose their settings if there's a power failure.

Installation's always quick and easy. And with our durable construction, you can count on many years of dependable service. For convenience and value, you can't go wrong with P&S Harmony Dimmers.

Attractive
P&S
Decorator
style

Pass & Seymour




Green LED glows when off — to make dimmer easy to find in the dark.

Sleek, ergonomic P&S Decorator style matches other Decorator devices.

Convenient operation — combines On/Off Decorator switch with separate slider for dimming control.

Constant memory returns lights to previous level after a power failure.



D703P-W

Cat. No.	Description	Rating
D703P*	Incandescent Single Pole/3-Way	700W
D1103P*	Incandescent Single Pole/3-Way	1100W
DLV703P*	Magnetic Low Voltage Single Pole/3-Way	700VA
DLV1103P*	Magnetic Low Voltage Single Pole/3-Way	1100VA
DFB8P*	120V Two-Wire Fluorescent Single Pole/3-Way	8A
DDH16P*	De-Hummer Fan Speed Control	1.6A

* Color Designation	
I	Ivory
LA	Light Almond
W	White
BK	Black
-	Brown

All devices are UL Listed and CSA Certified.

D703P, D1103P and DDH16P are available in VisionPak™. Add [V] after the color code.

DFB8P for use with Advance MK10 dimming ballasts.

For additional technical or application-specific information, call 800-223-4185 or visit our website at www.passandseymour.com. We're eager to put our expertise to work for you.

Distributed by:

USA
P.O. Box 4822
Syracuse, NY 13221-4822
800-611-7277

Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
905-738-9195

Pass & Seymour