

Eaton DG325URK

Catalog Number: DG325URK

Eaton General duty non-fusible safety switch, single-throw, 400 A, NEMA 3R, Rainproof, Painted galvanized steel, Three-pole, Three-wire, 240 V



Photo is representative

General specifications

Product Name

Eaton general duty non-fusible safety switch

Catalog Number

DG325URK

UPC

782113589541

Product Length/Depth

7.27 in

Product Height

44.74 in

Product Width

23.08 in

Product Weight

120 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

Drilled to accept field installed neutral kits

Type

Non-fusible, single-throw

Amperage Rating

400A

Number Of Poles

Three-pole

Product Category

General duty safety switch

Voltage rating

240V

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Number of wires

3

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DG325URK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)

Eaton DG325URK

Catalog Number: DG325URK

Eaton General duty non-fusible safety switch, single-throw, 400 A, NEMA 3R, Rainproof, Painted galvanized steel, Three-pole, Three-wire, 240 V



Photo is representative

General specifications

Product Name

Eaton general duty non-fusible safety switch

Catalog Number

DG325URK

UPC

782113589541

Product Length/Depth

7.27 in

Product Height

44.74 in

Product Width

23.08 in

Product Weight

120 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

Drilled to accept field installed neutral kits

Type

Non-fusible, single-throw

Amperage Rating

400A

Number Of Poles

Three-pole

Product Category

General duty safety switch

Voltage rating

240V

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Number of wires

3

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DG325URK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)