



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH362UWK 60A/3P HD NF Safety Switch 600V Nema 4X SS

Eaton Corp

Catalog Number	DH362UWK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Non-Fused Safety Switch, Single-Throw, 60 A, Nema 4X, Stainless Steel, Non-Fusible, Three-Pole, Three-Wire, 10 At 240 Vac TD 1 PH, 20 At 480 Vac TD 1 PH, 20 At 240 Vac TD 3 PH, 50 At 480 Vac TD 3 PH
Weight per unit	17.0 (lbs/each)
Product Category	Non-Fusible Heavy Duty Safety

Features

amperage rating	60 A
dimensions	10.2200 IN X 8.7600 IN X 14.1400 IN
Material	Stainless Steel
media	Yes
Poles	Three-pole
Voltage Rating	600 V

Descriptions

Description	60A/3P HD NF SAFETY SWITCH 600V NEMA 4X SS
extra long description	ETN DH362UWK 60A/3P HD NF Sfty Sw 6
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 60 A, NEMA 4X, Stainless steel, Non-Fusible, Three-pole, Three-wire, 10 at 240 Vac TD 1 Ph, 20 at 480 Vac TD 1 Ph, 20 at 240 Vac TD 3 Ph, 50 at 480 Vac TD 3 Ph
Product Type	60A/3P HD NF Sfty SW 600V N4X SS

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113206172
Manufacturers Part Number	DH362UWK
UPC	782113206172

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Non-Fusible Safety Switch

Packaging

Carton	1
Weight Per each	17



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Power

Distribution and Controls

nema rating

NEMA 4X

standard

UL Listed, NEC 230.62 (C) Compliant Barrier