



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 E J J Dr.
27406-0000, NC Greensboro
Phone: 336-743-0779
Fax: 000-000-0000



DH323NRK 100A/3P HD Fusible Safety Switch W/Neut 240V Nema *Eaton Corp*

Catalog Number	DH323NRK
Manufacturer	Eaton Corp
Description	Eaton Enhanced Visible Blade Single-Throw Safety Switch, 100 A, Nema 3R, Painted Galvanized Steel, Class H, Fusible With Neutral, Three-Pole, Four-Wire, 240 V, Max HP: 7.5, 15/ 15, 30/ 20 HP (1, 3PH @STD/TD/250 VDC), #14-#1/0 Cu/Al
Weight per unit	27.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	100
Material	Galvanized Steel
media	Yes
Poles	Three-pole
Voltage Rating	240V

Dimensions and Weight

Depth	22.5
Height	9
Width	12.75

Descriptions

Description	100A/3P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA
extra long description	ETN DH323NRK 100A/3P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Enhanced visible blade single-throw safety switch, 100 A, NEMA 3R, Painted galvanized steel, Class H, Fusible with neutral, Three-pole, Four-wire, 240 V, Max Hp: 7.5, 15/ 15, 30/ 20 hp (1,3PH @Std/TD/250 Vdc), #14-#1/0 Cu/Al
Product Type	100A/3P HD FSBL Sfty SW W/Neut 240V N3R

Manufacturer Information

Brand	Eaton
GTIN	00782113206271
Manufacturers Part Number	DH323NRK
UPC	782113206271

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 E J J Dr.
27406-0000, NC Greensboro
Phone: 336-743-0779
Fax: 000-000-0000

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
--------	---

Weight Per each	27
-----------------	----

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power
-------------	---

	Distribution and Controls
--	---------------------------

nema rating	3R
-------------	----

standard	UL Listed
----------	-----------