



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH327NRK 800A/3P HD Fusible Safety Switch W/Neut 240V Nema

Eaton Corp

Catalog Number	DH327NRK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 800 A, Nema 3R, Painted Galvanized Steel, Class L, Fusible With Neutral, Three-Pole, Four-Wire, 240 V, Max HP: 100 HP (3PH @STD), (4)#1/0-(4)750 Kcmil Al
Weight per unit	168.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	800A
dimensions	57.5000 IN X 27.5000 IN X 12.3800 IN
Material	Painted galvanized steel
media	Yes
Poles	Three-pole
Voltage Rating	240V

Descriptions

Description	800A/3P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA
extra long description	ETN DH327NRK 800A/3P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 800 A, NEMA 3R, Painted galvanized steel, Class L, Fusible with neutral, Three-pole, Four-wire, 240 V, Max Hp: 100 hp (3PH @Std), (4)#1/0-(4)750 kcmil Al
Product Type	800A/3P HD FSBL Sfty SW W/Neut 240V N3R

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113639253
Manufacturers Part Number	DH327NRK
UPC	782113639253

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch

Packaging

Carton	1
Weight Per each	168



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Power

Distribution and Controls

nema rating

Nema 3R

standard

UL Listed, NEC 230.62 (C) Compliant Barrier