



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH363UWK 100A/3P HD NF Safety Switch 600V N4X SS

*Eaton Corp*

Catalog Number	DH363UWK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Non-Fused Safety Switch, 100 A, Nema 4X, Stainless Steel, Non-Fusible, Three-Pole, Three-Wire, 20 At 240 Vac TD 1 PH, 40 At 480 Vac TD 1 PH, 50 At 600 Vac TD 1 PH, 40 At 240 Vac TD 3 PH, Single-Throw
Weight per unit	24.2 (lbs/each)
Product Category	Non-Fusible Heavy Duty Safety

### Features

amperage rating	100
Material	Stainless Steel
media	Yes
Poles	Three-pole
Voltage Rating	600 V

### Dimensions and Weight

Depth	10.22
Height	24.95
Width	11.79

### Descriptions

Description	100A/3P HD NF SAFETY SWITCH 600V N4X SS
extra long description	ETN DH363UWK 100A/3P HD NF Sfty Sw
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw non-fused safety switch, 100 A, NEMA 4X, Stainless steel, Non-Fusible, Three-pole, Three-wire, 20 at 240 Vac TD 1 Ph, 40 at 480 Vac TD 1 Ph, 50 at 600 Vac TD 1 Ph, 40 at 240 Vac TD 3 Ph, Single-throw
Product Type	100A/3P HD NF Sfty SW 600V N4X SS

### Manufacturer Information

Brand	Eaton
GTIN	00782113206578
Manufacturers Part Number	DH363UWK
UPC	782113206578

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Non-Fusible Safety Switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1

Weight Per each ..... 24.2

## Uses, Certifications, and Standards

Application ..... Commercial / Institutional Buildings / Structures - Power

..... Distribution and Controls

nema rating ..... 4X

standard ..... UL Listed, NEC 230.62 (C) Compliant Barrier