



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **E34PB1 Flush PB BK** *Eaton Corp*

Catalog Number	E34PB1
Manufacturer	Eaton Corp
Description	Eaton, 30.5 MM Watertight/Oiltight Hazardous Locations Pushbutton, Black, Plastic Actuator, Non-Illuminated, Flush Mounting, Nema 3, 3R, 4, 4X, 12, 13, Momentary, 30.5 MM, Flush Pushbutton, E34 Series
Weight per unit	0.2500 (lbs/each)
Product Category	Push Button Components

### **Features**

dimensions	1.9000 IN X 1.9000 IN X 2.1000 IN
media	Yes

### **Dimensions and Weight**

Depth	1.9000
Height	2.1000
Size	30.5 MM
Width	1.9000

### **Descriptions**

Description	FLUSH PB BK
extra long description	ETN E34PB1 FLUSH PB BK
Features	The two-layer, 100 percent solid thermosetting cathodic epoxy coating applied to these rugged, die cast pushbuttons provides a flat black, smooth, consistent and corrosion-resistant surface that has passed a demanding 600-hour salt spray test—four times longer than the industry-standard test.
Long Description	Eaton, 30.5 mm Watertight/Oiltight Hazardous Locations Pushbutton,Black,Plastic Actuator,Non-illuminated,Flush mounting,NEMA 3, 3R, 4, 4X, 12, 13,Momentary,30.5 mm,Flush Pushbutton,E34 Series
Product Type	Flush PB BK

### **Manufacturer Information**

Brand	EATON CUTLER-HAMMER
GTIN	00782113704265
Manufacturers Part Number	E34PB1
Model	Pushbutton
UPC	782113704265

### **Taxonomies, Classifications, and Categories**

Category Description	PUSHBUTTONS & CHIMES
Type	PUSHBUTTON



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.25

## Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
Mounting standard	FLUSH UL Listed, CSA Certified, FDA 3-A, CE Marked