



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E50DT2 E50 Heavy Duty Limit Switch

Eaton Corp

Catalog Number	E50DT2
Manufacturer	Eaton Corp
Description	Eaton E50 Nema Heavy Duty Plug-In Limit Switch, Adjustable Spring Return, Die Cast Zinc, Nema 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, 14° to 201°F (-10° to 94°C), E50
Weight per unit	0.1100 (lbs/each)
Product Category	Limit Switch Heads

Features

dimensions	2.0500 IN X 1.5400 IN X 1.7800 IN
Material	Die Cast Zinc

Descriptions

Description	E50 HEAVY DUTY LIMIT SWITCH
extra long description	ETN E50DT2 E50 HEAVY DUTY LIMIT SWI
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	Eaton E50 NEMA heavy duty plug-in limit switch, Adjustable spring return, Die cast zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, 14° to 201°F (-10° to 94°C), E50
Product Type	E50 Heavy Duty Limit Switch

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113290607
Manufacturers Part Number	E50DT2
UPC	782113290607

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch

Packaging

Carton	1
Weight Per each	0.11



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Water and Wastewater Systems - Water and Wastewater
Systems - OtherStationary Mach Equip In Factory - Machine
Tools: CuttingStationary Mach Equip In Factory - Machine Tools:
Forming

Operating Temperature
standard

14
CSA Certified,UL Recognized,RoHS Compliant