



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EC0101 3/4" Weatherhead *Appleton/Oz Gedney*

Catalog Number	EC0101
Manufacturer	Appleton/Oz Gedney
Description	Features:3.64IN Depth X 2.8IN Height, (2) 3/8 In, (3) 13/32 In Holes, Weather Resistant, For Threaded/Unthreaded Rigid Conduit, Imc/Emt Service Masts, Standard:UL 514B, Nema FB-1, Size:0.75IN, Material:Die Cast Zinc, Finish:Natural
Weight per unit	0.2900 (lbs/each)
Product Category	Service Entrance CBL Fittings

Features

Material	Die Cast Zinc
----------	---------------

Material, Color, and Finish

Finish	Unfinished
--------	------------

Dimensions and Weight

Size	0.75
------	------

Descriptions

Description	3/4" WEATHERHEAD
extra long description	EGS ECO-101 3/4 IN ALUM CLP ON ENTR
Long Description	Features:3.64IN Depth X 2.8IN Height, (2) 3/8 IN, (3) 13/32 IN Holes, Weather Resistant, For Threaded/Unthreaded Rigid Conduit, IMC/EMT Service Masts, Standard:UL 514B, NEMA FB-1, Size:0.75IN, Material:Die Cast Zinc, Finish:Natural
Product Type	3/4 In Alum CLP On Entr Cap
Special Features	3.64 IN Depth X 2.8 IN Height, (2) 3/8 IN, (3) 13/32 IN Holes, Weather Resistant, For Threaded/Unthreaded Rigid Conduit, IMC/EMT Service Masts

Manufacturer Information

Brand	Appleton
GTIN	00687855251018
Manufacturers Part Number	ECO-101
UPC	687855251018

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Clamp-On Entrance Cap



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	50
Weight Per each	0.29

Uses, Certifications, and Standards

Application	Clamp on Type For Use With Threaded or Unthreaded EMT or IMC Conduit
standard	UL 514B, NEMA FB-1