



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2900 East Pioneer Parkway Suite 170
76010-0000, TX Arlington
Phone: 817-695-1616
Fax: 817-633-9062



ECBRLEDM6 120/277V Led Exit W/ Led Lightbar Red

Lithonia Lighting - Acuity

Catalog Number	ECBRLEDM6
Manufacturer	Lithonia Lighting - Acuity
Description	Red, Integrated Exit/Unit Combos, Led, Sku - 210LCV
Weight per unit	3.3 (lbs/each)
Product Category	Exit Signs

Features

Fixture Type	Emergency Exit Unit (aka Combo)
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
Lamp Wattage	Not Applicable
lumens	184 LM
Material	Thermoplastic
Maximum Operating Temperature	50
Number of Lamps	Not Applicable
pallet quantity	360
Power Source	Hardwired
Shape	Square
Voltage Rating	120/277
Warranty	2
Wattage	3

Material, Color, and Finish

Background Color	White
Color	White
Finish	Matte
housing color	White
Lens Material	Plastic
Letter Color	RED

Dimensions and Weight

Height	8.25
Length	12.625
Width	1.875



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2900 East Pioneer Parkway Suite 170
76010-0000, TX Arlington
Phone: 817-695-1616
Fax: 817-633-9062

Descriptions

Description	120/277V LED EXIT W/ LED LIGHTBAR RED
extra long description	LITH ECBR LED M6 Red, integrated ex
Long Description	Red, Integrated Exit/Unit Combos, LED, SKU - 210LCV
Product Type	Emergency Lighting Unit
Special Features	Energy - efficient LED exit sign with integrated LED light bar, into one low-profile unit.

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00784231874912
Manufacturers Part Number	ECBR LED M6
UPC	784231874912

Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
Type	Emergency Exit Unit (aka Combo)

Packaging

Carton	1
Package	6
Weight	2.95
Weight Per each	3.3

Uses, Certifications, and Standards

Application	Education,Government,Healthcare,Offices & Banks,Retail
environmental conditions	Indoor
Mounting	SURFACE
standard	NFPA 101,NFPA 70,ULCA Title 20