

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4955 Bell Springs Rd Unit 9 78620-0000, TX Dripping Springs Phone: 737-317-5073 Fax: 737-317-5074



### EC0106 2-1/2" Weatherhead Appleton/Oz Gedney

Catalog Number	EC0106
Manufacturer	Appleton/Oz Gedney
Description	Features:10.5IN Depth X 7IN Height, (3) 7/8 In, (1) 1 In, (3) 1 5/16 In Holes, Weather Resistant, For Threaded/Unthreaded Rigid Conduit, Imc/Emt Service Masts, Standard:UI 514B, Nema FB-1, Size:2.5IN, Material:Aluminum, Finish:Natural
Weight per unit	3.9 (lbs/each)
Product Category	Service Entrance CBL Fittings
Features	
Material	Aluminum
Material, Color, and Finish	
Finish	Unfinished
<b>Dimensions and Weight</b>	
Size	2.5
Descriptions	
Description	2-1/2" WEATHERHEAD
extra long description	EGS ECO-106 2-1/2 IN ALUM CLP ON EN
Long Description	Features:10.5IN Depth X 7IN Height, (3) 7/8 IN, (1) 1 IN, (3) 1 5/16 IN Holes, Weather Resistant, For Threaded/Unthreaded Rigid Conduit, IMC/EMT Service Masts, Standard:UL 514B, NEMA FB-1, Size:2.5IN, Material:Aluminum, Finish:Natural
Product Type	2-1/2 In Alum CLP On Entr Cap
Special Features	10.5 IN Depth X 7 IN Height, (3) 7/8 IN, (1) 1 IN, (3) 1 5/16 IN Holes, Weather Resistant, For Threaded/Unthreaded Rigid Conduit, IMC/EMT Service Masts
Manufacturer Information	
Brand	Appleton
GTIN	00687855251063
Manufacturers Part Number	EC0106
UPC	687855251063
Taxonomies, Classifications, and C	<u> </u>
Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding

### Tax

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding
	Fittings & Ground Rods
Туре	Clamp-On Entrance Cap

#### **Packaging**

Carton	1
Weight Per each	3.85



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4955 Bell Springs Rd Unit 9 78620-0000, TX Dripping Springs Phone: 737-317-5073 Fax: 737-317-5074

#### **Uses, Certifications, and Standards**

Application	Clamp on Type For Use With Threaded or Unthreaded EMT or
	IMC Conduit
standard	UL 514B, NEMA FB-1