



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ECN5452AALP6R63G Pump Panel - 400A Fusible SW Nema 3R SZ 5 120VAC C *Eaton Corp*

Catalog Number	ECN5452AALP6R63G
Manufacturer	Eaton Corp
Description	Eaton Freedom Industrial Pump Panel, Fusible Disconnect, Nema 3R Painted Steel Enclosure, 120V/60 HZ, 110V/50 HZ Coil, 400A/600V Type R Fuse Clip, 60-300A Solid-State Electronic Overload Relay, Nema Size 5 Frame, Pushbutton Omitted
Weight per unit	150.0 (lbs/each)
Product Category	Reversing Starters With Circui

Features

Coil Voltage	120V/60 Hz, 110V/50 Hz
dimensions	62.0000 IN X 30.0000 IN X 21.0000 IN

Descriptions

Description	PUMP PANEL - 400A FUSIBLE SW NEMA 3R SZ 5 120VAC C
extra long description	ETN ECN5452AAL-P6R63/G PP 400A FUS
Features	Eaton's industrial pump panels are combination starters that are designed for irrigation, oil well, gas and other pump applications. The enclosure is NEMA Type 3R to provide weather-tight protection and is available in several sizes, depending on the customer's control option requirements. The disconnect, contactor and overload relay are the same as used in Freedom lines of combination starters.
Long Description	Eaton Freedom Industrial Pump Panel, Fusible disconnect, NEMA 3R Painted steel enclosure, 120V/60 Hz, 110V/50 Hz coil, 400A/600V Type R fuse clip, 60-300A solid-state electronic overload relay, NEMA size 5 frame, Pushbutton omitted
Product Type	PP 400A Fus SW N3R SZ5 120V CL

Manufacturer Information

Brand	Eaton
GTIN	00786685455440
Manufacturers Part Number	ECN5452AAL-P6R63/G
UPC	786685455440

Taxonomies, Classifications, and Categories

Category Description	PUMP PANELS
Type	Industrial Pump Panel

Packaging

Carton	1
Weight Per each	150



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Ind Facilities & Factories - Industrial Facilities/Factories -
OtherStationary Machinery and Equipment Outside Factory -
Pumps and Compressors

standard

UL Listed,cUL Listed,OSHPD Certified,ABS Certified