



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ECSR30 30A 600V Class RK5 Time Delay CL Fuse

*Edison Fuses*

Catalog Number	ECSR30
Manufacturer	Edison Fuses
Description	Time Delay Power Fuse, RK5 Class Fuse, Ferrule Fuse, 10 S @ 500% Response Time, Ferrule End X Ferrule End Connection, 30 A, 600 V Ac, Ferrule Terminal, 0.81 In Diameter, 5 In Overall Length, 0.50 LB
Weight per unit	0.1600 (lbs/each)
Product Category	Dual Element

### Features

Characteristics	10 SEC TIME DELAY (AT 500 PERCENT RATED LOAD), DUAL ELEMENT
Interrupting Rating	200 KILOAMPERE (SYMMETRICAL)

### Dimensions and Weight

Length	5 INCH
--------	--------

### Descriptions

Additional Information	Application Branch and Feeder Circuit, AC Drive, Loadcenter, Panel Board and Switch Board, Non-Inductive Load, General Purpose, Lighting and Heating
Commodity Description	DUAL ELEMENT FUSES
Description	30A 600V CLASS RK5 TIME DELAY CL FUSE
extra long description	CLASS RK5 TYPE; 5 INCH; UL, CSA C22.2, CE APPROVAL; 600 VAC VOLTAGE RATING; 0.81 INCH DIAMETER; 200 KILOAMPERE (SYMMETRICAL) INTERRUPTING RATING; 30 AMPERE CURRENT RATING; FERRULE TERMINAL TYPE; 10 SEC TIME DELAY (AT 500 PERCENT RATED LOAD), DUAL ELEMENT CHARACTERISTICS; APPLICATION BRANCH AND FEEDER CIRCUIT, AC DRIVE, LOADCENTER, PANEL BOARD AND SWITCH BOARD, NON-INDUCTIVE LOAD, GENERAL PURPOSE, LIGHTING AND HEATING; ECSR MODEL

### Manufacturer Information

GTIN	00782634508342
Model	ECSR
UPC	782634508342

### Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	CLASS RK5



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.16

## Uses, Certifications, and Standards

Approval	UL, CSA C22.2, CE
----------	-------------------