



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ECSR60 60A 600V Class RK5 Time Delay CL Fuse

Edison Fuses

Catalog Number	ECSR60
Manufacturer	Edison Fuses
Description	Time Delay Power Fuse, RK5 Class Fuse, Ferrule Fuse, 10 S @ 500% Response Time, Ferrule End X Ferrule End Connection, 60 A, 600 V Ac, Ferrule Terminal, 1.06 In Diameter, 5.5 In Overall Length, 3.10 LB
Weight per unit	0.3000 (lbs/each)
Product Category	Dual Element

Features

Characteristics	10 SEC TIME DELAY (AT 500 PERCENT RATED LOAD), DUAL ELEMENT
Interrupting Rating	200 KILOAMPERE (SYMMETRICAL)

Dimensions and Weight

Length	5.5 INCH
--------	----------

Descriptions

Additional Information	Application Branch and Feeder Circuit, AC Drive, Loadcenter, Panel Board and Switch Board, Non-Inductive Load, General Purpose, Lighting and Heating
Commodity Description	DUAL ELEMENT FUSES
Description	60A 600V CLASS RK5 TIME DELAY CL FUSE
extra long description	CLASS RK5 TYPE; 5.5 INCH; UL, CSA C22.2, CE APPROVAL; 600 VOLT AC VOLTAGE RATING; 1.06 INCH DIAMETER; 200 KILOAMP (SYMMETRICAL) INTERRUPTING RATING; 60 AMP CURRENT RATING; FERRULE TERMINAL TYPE; 10 SEC TIME DELAY (AT 500 PERCENT RATED LOAD), DUAL ELEMENT CHARACTERISTICS; APPLICATION AC POWER DISTRIBUTION SYSTEM MAINS, FEEDERS AND BRANCH CIRCUITS, PROTECTION OF MOTORS AND MOTOR BRANCH CIRCUITS, TRANSFORMERS AND OTHER INDUCTIVE LOADS, LIGHTING, HEATING AND OTHER NON-INDUCTIVE LOADS; ECSR MODEL

Manufacturer Information

GTIN	00782634508397
Model	ECSR
UPC	782634508397

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	CLASS RK5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.3

Uses, Certifications, and Standards

Approval	UL, CSA C22.2, CE
----------	-------------------