



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ECN5432AAGE3P6R6 Pump Panel - 100A Fusible SW Nema 3R SZ 3 120VAC C *Eaton Corp*

Catalog Number	ECN5432AAGE3P6R6
Manufacturer	Eaton Corp
Description	Eaton Freedom Industrial Pump Panel, Fusible Disconnect, Nema 3R Oversize Painted Steel Enclosure, 120V/60 HZ, 110V/50 HZ Coil, 100A/600V Type R Fuse Clip, 20-100A Solid-State Overload Relay, Nema Size 3 Frame, Pushbutton Omitted
Weight per unit	75.0 (lbs/each)
Product Category	Reversing Starters With Circui

Features

Coil Voltage	120V/60 Hz, 110V/50 Hz
dimensions	40.0000 IN X 20.0000 IN X 12.0000 IN

Descriptions

Description	PUMP PANEL - 100A FUSIBLE SW NEMA 3R SZ 3 120VAC C
extra long description	ETN ECN5432AAG-E3P6R63/E PP 100A FU
Features	Eaton's industrial pump panels are combination starters that are designed for irrigation, oil well, gas and other pump applications. The enclosure is NEMA Type 3R to provide weather-tight protection and is available in several sizes, depending on the customer's control option requirements. The disconnect, contactor and overload relay are the same as used in Freedom lines of combination starters.
Long Description	Eaton Freedom Industrial Pump Panel, Fusible disconnect, NEMA 3R oversize Painted steel enclosure, 120V/60 Hz, 110V/50 Hz coil, 100A/600V Type R fuse clip, 20-100A solid-state overload relay, NEMA size 3 frame, Pushbutton omitted
Product Type	PP 100A Fus SW N3R SZ3 120V CL

Manufacturer Information

Brand	Eaton
GTIN	00786685455426
Manufacturers Part Number	ECN5432AAG-E3P6R63/E
UPC	786685455426

Taxonomies, Classifications, and Categories

Category Description	PUMP PANELS
Type	Industrial Pump Panel

Packaging

Carton	1
Weight Per each	75



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Ind Facilities & Factories - Industrial Facilities/Factories -
OtherStationary Machinery and Equipment Outside Factory -
Pumps and Compressors

standard

UL Listed,OSHPD Certified,ABS Certified,cUL Listed