

# Eaton ED3225

Catalog Number: ED3225

Eaton Series C complete molded case circuit breaker, F-frame molded case circuit breaker, 225 A, Three- pole, Fixed thermal magnetic trip, ED breaker



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Series C complete molded case circuit breaker	ED3225
	UPC
	786679455081
<b>Product Length/Depth</b>	<b>Product Height</b>
3.38 in	6 in
<b>Product Width</b>	<b>Product Weight</b>
4.13 in	4.5 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## defaultTaxonomyAttributeLabel

### Amperage Rating

225 A

### Voltage rating

240 Vac, 125 Vdc

### Trip Type

Fixed thermal, fixed magnetic

### Circuit breaker type

ED

### Circuit breaker frame type

Complete breaker

### Series

Series C

### Terminals

Line and load

### Frame

F

### Frequency rating

50 to 60 Hz

### Interrupt rating

65 kAIC at 240 Vac

### Number of poles

Three-pole

## Resources

### Application notes

UL listed 100%-rated molded case circuit breakers

Application of Multi-Wire Terminals for Molded Case Circuit Breakers

Application of Tap Rules to Molded Case Breaker Terminals

### Brochures

Circuit breaker motor operators product aid

Power metering and monitoring with Modbus RTU product aid

Plug-in adapters for molded case circuit breakers product aid

Motor protection circuit breakers product aid

MOEM MCCB Product Selection Guide

StrandAble terminals product aid

Multi-wire lugs product aid

Current limiting Series C molded case circuit breakers product aid

Counterfeit and Gray Market Awareness Guide

Breaker service centers

### Catalogs

Molded case circuit breakers catalog

Eaton's Volume 4—Circuit Protection

### Drawings

FD3 2D Drawing Xchange

FD3 3D Model Xchange

Time Current Curves for Series C® F-Frame Circuit Breakers

FD3 2D PDF

F-frame Molded Case Circuit Breaker Drawing

FD3 3D Inventor

### Installation instructions

Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches

### Multimedia

Circuit Breakers Explained

Circuit breakers explained

### Specifications and datasheets

Eaton Specification Sheet - ED3225

Series C J-Frame molded case circuit breakers time current curves

Series C F-Frame molded case circuit breakers

MOEM MCCB product selection guide

Series C G-Frame molded case circuit breakers time current curves

F-Frame 310+ Molded-case circuit breakers 15-225A



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)