

Eaton ECN5532CAG

Catalog Number: ECN5532CAG

Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, NEMA 3R painted steel enclosure, 440V/50 Hz-460V/60 Hz coil, NEMA size 3, 100A breaker



General specifications

Product Name	Catalog Number
Eaton Industrial pump panel	ECN5532CAG
UPC	Product Length/Depth
782114139134	8.47 in
Product Height	Product Width
38.4 in	18.86 in
Product Weight	Warranty
75 lb	1 year
Certifications	
cUL Listed	
OSHDP Certified	
UL Listed	

Coil voltage

440V/50 Hz-460V/60 Hz

Enclosure

NEMA 3R

Enclosure material

Painted steel

Type

Circuit breaker disconnect

Circuit breaker rating

100A

Size

NEMA size 3

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Specifications and datasheets

[Eaton Specification Sheet - ECN5532CAG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)

Eaton ECN5532CAG

Catalog Number: ECN5532CAG

Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, NEMA 3R painted steel enclosure, 440V/50 Hz-460V/60 Hz coil, NEMA size 3, 100A breaker



General specifications

Product Name	Catalog Number
Eaton Industrial pump panel	ECN5532CAG
UPC	Product Length/Depth
782114139134	8.47 in
Product Height	Product Width
38.4 in	18.86 in
Product Weight	Warranty
75 lb	1 year
Certifications	
cUL Listed	
OSHDP Certified	
UL Listed	

Coil voltage

440V/50 Hz-460V/60 Hz

Enclosure

NEMA 3R

Enclosure material

Painted steel

Type

Circuit breaker disconnect

Circuit breaker rating

100A

Size

NEMA size 3

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Specifications and datasheets

[Eaton Specification Sheet - ECN5532CAG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)