

# Eaton ED2200

Catalog Number: ED2200

Eaton Series C complete molded case circuit breaker, F-frame molded case circuit breaker, 200 A, Two - pole, Fixed thermal magnetic trip, ED breaker



Photo is representative

## General specifications

| Product Name   | Catalog Number |
|--|----------------|
| Eaton Series C complete molded case circuit breaker  | ED2200         |
|  | UPC            |
|  | 786679456224   |
| Product Length/Depth   | Product Height |
| 3.38 in  | 6 in           |
| Product Width  | Product Weight |
| 2.75 in  | 2.9 lb         |
| Warranty   | Certifications |
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |                |

## defaultTaxonomyAttributeLabel

### Amperage Rating

200 A

### Voltage rating

240 Vac, 125 Vdc

### Trip Type

Fixed thermal, fixed magnetic

### Circuit breaker type

ED

### Circuit breaker frame type

Complete breaker

### Series

Series C

### Terminals

Line and load

### Frame

F

### Frequency rating

50 to 60 Hz

### Interrupt rating

65 kAIC at 240 Vac

### Number of poles

Two-pole

## Resources

### Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

### Brochures

[Multi-wire lugs product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Circuit breaker motor operators product aid](#)

[Motor protection circuit breakers product aid](#)

[MOEM MCCB Product Selection Guide](#)

[StrandAble terminals product aid](#)

[Breaker service centers](#)

[Counterfeit and Gray Market Awareness Guide](#)

### Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

### Drawings

[FD2 2D Drawing Xchange](#)

[FD2 3D Model Xchange](#)

[FD2 2D PDF](#)

[Time Current Curves for Series C® F-Frame Circuit Breakers](#)

[FD2 3D Inventor](#)

[F-frame Molded Case Circuit Breaker Drawing](#)

### Installation instructions

[Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)

### Multimedia

[Circuit breakers explained](#)

[Circuit Breakers Explained](#)

### Specifications and datasheets

[Series C F-Frame molded case circuit breakers](#)

[F-Frame 310+ Molded-case circuit breakers 15-225A](#)

[Eaton Specification Sheet - ED2200](#)

[Series C J-Frame molded case circuit breakers time current curves](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)