



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8620 E 34th St N
67226-0000, KS Wichita
Phone: 316-247-8220
Fax: 000-000-0000



EDGR1RMRELM4 Recessed Mount Edge-Lit E

Lithonia Lighting - Acuity

Catalog Number	EDGR1RMRELM4
Manufacturer	Lithonia Lighting - Acuity
Description	Recessed Mount Edge-Lit Exits With Led Lamps, Single Face, Red With Mirror Separator, Emergency, Sku - 211MHK
Weight per unit	4.4 (lbs/each)
Product Category	Exit Signs

Features

average life	Not Applicable
battery	4.8 volts
dimensions	Not Applicable
Fixture Type	Exit Sign
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
Material	Aluminum
Power Source	Hardwired
Shape	Square
Voltage Rating	120,277 V
Warranty	5
Wattage	3

Material, Color, and Finish

Color	Silver
Lens Material	Not Applicable

Dimensions and Weight

Height	4.0
Length	13.75
Width	8.00



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8620 E 34th St N
67226-0000, KS Wichita
Phone: 316-247-8220
Fax: 000-000-0000

Descriptions

Description	RECESSED MOUNT EDGE-LIT E
extra long description	LITH EDGR 1 RMR EL M4 Recessed moun
Features	Design Select
Long Description	Recessed mount Edge-Lit exits with LED lamps, Single face, Red with mirror separator, Emergency, SKU - 211MHK
Product Type	Emergency Exit Sign
Special Features	The versatile EDG/EDGR edge-lit exits are well suited for any application requiring attractive edge-lit exit signage. Typical installations include commercial spaces such as retail, offices or medical facilities but can be applied in any space where an upgraded appearance is desired.

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00753573029007
Manufacturers Part Number	EDGR 1 RMR EL M4
UPC	753573029007

Taxonomies, Classifications, and Categories

Type	Exit Sign
------	-----------

Packaging

Carton	1
Weight	5.65
Weight Per each	4.44

Uses, Certifications, and Standards

Application	Education,Government,Healthcare,Hospitality,Offices & Banks,Retail,Sports and Recreation
environmental conditions	Indoor,Outdoor
Mounting	Recessed,Surface
standard	NFPA 101,ULBAA,CA Title 20