ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EGH3030FFG E 3P 30A 70KA @ 415 65KA @ 480V Fixed Thermal Fixe

Eaton Corp

Catalog Number	EGH3030FFG
Manufacturer	Eaton Corp
Description	Eaton Series G Molded Case Circuit Breaker, Eg-Frame, Eg, Fixed Thermal, Fixed Magnetic Trip, Three-Pole, 30 A, 600Y/347 Vac, 100 Kaic At 240 Vac, 65 Kaic At 480 Vac, 35 Kaic At 600Y/347 Vac, Line and Load, 50/60 HZ
Weight per unit	2.9 (lbs/each)
Product Category	3 Pole

Features

Current Rating	30 A
dimensions	2.9900 IN X 3.0000 IN X 5.5000 IN
frame	EG
interrupt rating	35 kAIC at 600Y/347 Vac65 kAIC at 480 Vac100 kAIC at 240 Vac
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	347/600

Descriptions

Description	E 3P 30A 70KA @ 415 65KA @ 480V FIXED THERMAL FIXE
extra long description	ETN EGH3030FFG E 3P 30A 70kA 415 65
Features	The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed “blow-open” action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren
Long Description	Eaton Series G molded case circuit breaker, EG-frame, EG, Fixed thermal, Fixed magnetic trip, Three-pole, 30 A, 600Y/347 Vac, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, 35 kAIC at 600Y/347 Vac, Line and load, 50/60 Hz
Product Type	E 3P 30A 70KA 415 65KA 480V FXD TM

Manufacturer Information

Brand	Eaton
GTIN	00782114877517
Manufacturers Part Number	EGH3030FFG
UPC	782114877517

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Powerdefense Breakers
Type	Molded case circuit breaker

Packaging

Carton	1
Weight Per each	2.89

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies and EOEMs - Other
Frequency Rating	50/60
standard	CSA Certified,IEC Rated,UL Listed,CE Marked