

Eaton EHD2020

Catalog Number: EHD2020

Eaton Series C complete molded case circuit breaker, F-frame, EHD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 20 A, Load side, 50/60 Hz

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	EHD2020
	UPC
	786679317426

Product Length/Depth	Product Height
3.38 in	6 in

Product Width	Product Weight
2.75 in	2.9 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

20 A

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

EHD

Circuit breaker frame type

Complete breaker

Series

Series C

Terminals

Load side

Frame

F

Frequency rating

50/60 Hz

Interrupt rating

14 kAIC at 480 Vac

18 kAIC at 240 Vac

Number of poles

Two-pole

Resources

Application notes

Application of Multi-Wire Terminals for Molded Case Circuit Breakers

UL listed 100%-rated molded case circuit breakers

Application of Tap Rules to Molded Case Breaker Terminals

Brochures

Multi-wire lugs product aid

Current limiting Series C molded case circuit breakers product aid

MOEM MCCB Product Selection Guide

Motor protection circuit breakers product aid

StrandAble terminals product aid

Circuit breaker motor operators product aid

Plug-in adapters for molded case circuit breakers product aid

Power metering and monitoring with Modbus RTU product aid

Counterfeit and Gray Market Awareness Guide

Breaker service centers

Catalogs

Eaton's Volume 4—Circuit Protection

Molded case circuit breakers catalog

Drawings

EHD2 2D PDF

EHD2 3D Model Xchange

Time Current Curves for Series C® F-Frame Circuit Breakers

F-frame Molded Case Circuit Breaker Drawing

EHD2 2D Drawing Xchange

EHD2 3D Inventor

Installation instructions

Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches

Multimedia

Circuit Breakers Explained

Circuit breakers explained

Specifications and datasheets

MOEM MCCB product selection guide

Eaton Specification Sheet - EHD2020

F-Frame 310+ Molded-case circuit breakers 15-225A

Series C F-Frame molded case circuit breakers

Series C G-Frame molded case circuit breakers time current curves

Series C J-Frame molded case circuit breakers time current curves

Time/current curves

Types EHD and FDB 10 Amperes AB DE-ION Circuit Breakers



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)