



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EMT11230 1-1/2", 30D Emt Elb

Robroy/Ecn Korns

Catalog Number	EMT11230
Manufacturer	Robroy/Ecn Korns
Description	Elbow, Standard Radius; Trade Size 1-1/2 Inch; 30 Deg Bend; 8.25 Inch Bend Radius; External Threaded End; Galvanized; Standard Package 20 Per Carton; Applicable Standard Ansi C80.3; Approval UI 797, Csa C22.2; Robroy[R] Brand; Emtelb Model
Weight per unit	1.6 (lbs/each)
Product Category	20190320151947

Features

Applicable Standard	ANSI C80.3
Bend Angle	30 DEG
Bend Radius	8.25 INCH
End Type	EXTERNAL THREADED
Trade Size - Fractional	1-1/2 IN Rating

Material, Color, and Finish

Finish	Galvanized
--------	------------

Descriptions

Also Known As...	Sweep Elbow Pre-Fab
Commodity Description	Elbows, Couplings, Nipples, Running Thread - Steel
Description	1-1/2",30D EMT ELB
Long Description	ELBOW, STANDARD RADIUS; TRADE SIZE 1-1/2 INCH; 30 DEG BEND; 8.25 INCH BEND RADIUS; EXTERNAL THREADED END; GALVANIZED; STANDARD PACKAGE 20 PER CARTON; APPLICABLE STANDARD ANSI C80.3; APPROVAL UL 797, CSA C22.2; ROBROY[R] BRAND; EMTELB MODEL

Manufacturer Information

Brand	Robroy/Ecn Korns
Manufacturers Part Number	EMTELB1-1/2X30
Model	EMTELB

Taxonomies, Classifications, and Categories

Category Description	EMT ELBOWS
Type	STANDARD RADIUS

Trade Size

Trade Size	1-1/2 INCH
Trade Size in inch	1.5 in in



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	20
Standard Package	20 PER CARTON
Weight Per each	1.58

Uses, Certifications, and Standards

Approval	UL 797, CSA C22.2
----------	-------------------