



**On-Q**  
**12-inch Enclosure with Screw-On Cover**  
Part No. EN1200



This 12-inch enclosure is the perfect solution for a basic or entry-level structured wiring system. It features large top openings that make pulling wire easier than ever before. The enclosure also boasts multiple knockouts, side lances, and side tabs

## Features & Benefits

12-in Enclosure with Screw-On Cover

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Literature pouch included for dealer information

Includes self-adhesive cable identification table

Cover included

Made in the USA :

## Specifications

### General Info

Product Line	On-Q	Color	White
UPC Number	804428050650	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

### Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	12.13 in	Enclosure Size	12 in

---

## Listing Agencies / 3rd Party Agencies

---

CSA Listed

Yes

cULus Listed

Yes

---

## Additional Information

---

RoHS Compliant

Yes

---

## Technical Information

---

Thickness

0.1 in

Cable Entry

(3) top knockouts

---

Frame

Cold Rolled Steel

---



**On-Q**  
**12-inch Enclosure with Screw-On Cover**  
Part No. EN1200



This 12-inch enclosure is the perfect solution for a basic or entry-level structured wiring system. It features large top openings that make pulling wire easier than ever before. The enclosure also boasts multiple knockouts, side lances, and side tabs

## Features & Benefits

12-in Enclosure with Screw-On Cover

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Literature pouch included for dealer information

Includes self-adhesive cable identification table

Cover included

Made in the USA :

## Specifications

### General Info

Product Line	On-Q	Color	White
UPC Number	804428050650	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

### Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	12.13 in	Enclosure Size	12 in

---

## Listing Agencies / 3rd Party Agencies

---

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

---

## Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

## Technical Information

---

Thickness	0.1 in	Cable Entry	(3) top knockouts
-----------	--------	-------------	-------------------

---

Frame	Cold Rolled Steel
-------	-------------------

---