



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ER53060UW Enclosed UL508 3P/60A Nema 4X SS *Eaton Corp*

Catalog Number	ER53060UW
Manufacturer	Eaton Corp
Description	Eaton Enclosed Rotary Disconnect Switch, 60 A, Nema 4X, Stainless Steel, Max HP:15, 15, 30, 30 HP (@208, 240, 480, 600 V), Three-Pole, Product Category: Enclosed Rotary Non-Fusible, R-Series, 600 V
Weight per unit	8.4 (lbs/each)
Product Category	Non-Fusible Disconnect Safety

Features

amperage rating	60A
dimensions	15.4000 IN X 10.0000 IN X 8.4000 IN
Material	Stainless Steel
media	Yes
Poles	Three-pole
Voltage Rating	600 V

Descriptions

Description	ENCLOSED UL508 3P/60A NEMA 4X SS
extra long description	ETN ER53060UW Enclosed, 60 A, Three
Features	Eaton's full-range of rotary disconnects offers a compact, economical, and high-quality choice for switching and isolation spanning a range from 16A - 1200A. The R5 Series of switches are UL 508 listed devices, suitable for use as motor disconnects. The R9 offering consists of UL 98 listed fusible and non-fusible products that may be used for service entrance, or anywhere a local means of disconnect is needed or required.
Long Description	Eaton enclosed rotary disconnect switch, 60 A, NEMA 4X, Stainless steel, Max HP:15, 15, 30, 30 hp (@208,240,480,600 V), Three-pole, Product category: enclosed rotary non-fusible, R-Series, 600 V
Product Type	Enclosed, 60 A, Three-Pole, 600 V, N4X

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685466125
Manufacturers Part Number	ER53060UW
UPC	786685466125

Taxonomies, Classifications, and Categories

Category Description	Rotary Disconnects
Type	Enclosed Rotary Disconnect Switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	8.3999

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
standard	UL Listed, CSA Certified