

DESCRIPTION

Specular Reflector trim in the 6" All-Pro trim family for use in Halo and All-Pro recessed downlighting.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Uses coil spring retention. Trim available in high gloss appliance white. Reflector available in clear specular and gold.

Lamp Listings - Incandescent

EI700	75W R30, 65W BR30, 50W PAR30, 75W PAR30L
EI700AT	
EI700R	50W PAR30, 75W PAR30L, 65W BR30, 75W R30
EI700RAT	

EI700U	75W PAR30, 75W PAR30L, 85W BR30, 90W BR40, 100W R30, 100W R40, 100W PAR38
EI700UAT	

ET2700	75W PAR30, 75W PAR30L, 85W BR30, 100W R30
ET2700R	65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 85W BR30


Lamp Listings - Incandescent

ET700	65W BR30, 75W R30, 75W PAR30, 150W R40, 150W PAR38
ET700R	65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 150W R40

EI2700	50W PAR30, 65W BR30, 75W R30, 75W PAR30L
EI2700AT	
EI2700R	

Lamp Listings - GU24

H724ICAT	CF15/R30/GU24
H724ICATL	
H724RICAT	CF13/GU24 (spiral)
H724RICATL	



Height: 2-7/8" [73mm]
Outside Diameter: 7-1/4" [184mm]

ORDERING INFORMATION

Trim

--

ERT710 = 6" High gloss appliance white trim with clear specular reflector
ERT710G = 6" High gloss appliance white trim with gold reflector



ERT710
Gloss White Trim,
Clear Specular Reflector



ERT710G
Gloss White Trim,
Gold Reflector

ERT710

6-Inch Specular Reflector

DESCRIPTION

Specular Reflector trim in the 6" All-Pro trim family for use in Halo and All-Pro recessed downlighting.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Uses coil spring retention. Trim available in high gloss appliance white. Reflector available in clear specular and gold.

Lamp Listings - Incandescent

EI700	75W R30, 65W BR30, 50W PAR30, 75W PAR30L
EI700AT	
EI700R	50W PAR30, 75W PAR30L, 65W BR30, 75W R30
EI700RAT	

EI700U	75W PAR30, 75W PAR30L, 85W BR30, 90W BR40, 100W R30, 100W R40, 100W PAR38
EI700UAT	

ET2700	75W PAR30, 75W PAR30L, 85W BR30, 100W R30
ET2700R	65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 85W BR30


Lamp Listings - Incandescent

ET700	65W BR30, 75W R30, 75W PAR30, 150W R40, 150W PAR38
ET700R	65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 150W R40

EI2700	50W PAR30, 65W BR30, 75W R30, 75W PAR30L
EI2700AT	
EI2700R	

Lamp Listings - GU24

H724ICAT	CF15/R30/GU24
H724ICATL	
H724RICAT	CF13/GU24 (spiral)
H724RICATL	



Height: 2-7/8" [73mm]
Outside Diameter: 7-1/4" [184mm]

ORDERING INFORMATION

Trim

--

ERT710 = 6" High gloss appliance white trim with clear specular reflector
ERT710G = 6" High gloss appliance white trim with gold reflector



ERT710
Gloss White Trim,
Clear Specular Reflector



ERT710G
Gloss White Trim,
Gold Reflector

ERT710

6-Inch Specular Reflector