

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

121 S 39th Ave #100 85009-0000, AZ Phoenix Phone: 480-372-4901 Fax: 480-372-4902



## **ESGTS2 #14-2 Awg Gel Tap Splice Kit (W/Connector)** *Nsi Industries*

Catalog Number	ESGTS2
Manufacturer	Nsi Industries
Description	Easy-Splice Gel Tap Splice Kit With Connector For #14 - #2 Awg The Easy-Splice Gel Tap Splice Kit Provides A Fast and Simple Method For Connecting, Insulating, and Environmentally Sealing Low-Voltage Splices. The Splice Kit Is Designed For Underground and Overhead Environments and Is Useful For Street Lighting Applications. The Splice Kit'S Dual-Rated Mechanical Connector Splices A Wide Range Of Cables, Including Copper and Aluminum. The Connector'S Four Port Design Allows Maximum Inventory Flexibility. TH
Weight per unit	0.1600 (lbs/each)
Product Category	Splicing & Terminating Kits
Features	
Cable Size	14-2 AWG
Cable Type	Class A-B
Voltage Rating	1000 V
Warranty	1 YEAR
Material, Color, and Finish	
Color	Black



## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

121 S 39th Ave #100 85009-0000, AZ Phoenix Phone: 480-372-4901 Fax: 480-372-4902

Descriptions	WAA O ANNO CEL TAD CDUICE WIT (AN/COMMECTOD)
Description	#14-2 AWG GEL TAP SPLICE KIT (W/CONNECTOR)
extra long description	NSI ESGTS-2 Easy-Splice Gel 2/0 SL
Features	Easy-Splice Gel Tap Splice Kit with Connector for #14 - #2 AWG The Easy-Splice gel tap splice kit provides a fast and simple method for connecting, insulating, and environmentally sealing low-voltage splices. The splice kit is designed for underground and overhead environments and is useful for street lighting applications. The splice kit's dual-rated mechanical connector splices a wide range of cables, including copper and aluminum. The connector's four port design allows maximum inventory flexibility. Th
Long Description	Easy-Splice Gel Tap Splice Kit with Connector for #14 - #2 AWG The Easy-Splice gel tap splice kit provides a fast and simple method for connecting, insulating, and environmentally sealing low-voltage splices. The splice kit is designed for underground and overhead environments and is useful for street lighting applications. The splice kit's dual-rated mechanical connector splices a wide range of cables, including copper and aluminum. The connector's four port design allows maximum inventory flexibility. Th
Product Type	Easy-Splice Gel 2/0 SL
Special Features	Four Port Design With Dual Rated Mecahnical Connector
Manufacturer Information	
Brand	NSi
GTIN	00662381168634
Manufacturers Part Number	ESGTS-2
UPC	662381168634
Taxonomies, Classifications, and Ca	ategories
Category Description	ODLIGE WITO
	Gel Tap Splice Kits With Connector
Packaging	
Carton	3
Weight Per each	
Uses, Certifications, and Standards	
Application	Splicing Wire

-40 C To 90 C

ANSI C119.1-1986 Qualified

**Operating Temperature** 

standard