



ESGTS20 #14-2/0 Awg Gel Tap Splice Kit (W/Connector)

Nsi Industries

Catalog Number	ESGTS20
Manufacturer	Nsi Industries
Description	Easy-Splice Gel Tap Splice Kit With Connector For #14 - 2/0 Awg The Easy-Splice Gel Tap Splice Kit Provides A Fast and Simple Method For Connecting, Insulating, and Environmentally Sealing Low-Voltage Splices. The Splice Kit Is Designed For Underground and Overhead Environments and Is Useful For Street Lighting Applications. The Splice Kit'S Dual-Rated Mechanical Connector Splices A Wide Range Of Cables, Including Copper and Aluminum. The Connector'S Four Port Design Allows Maximum Inventory Flexibility. T
Weight per unit	0.2600 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Cable Size	14-2/0 AWG
Cable Type	Class A-B
Voltage Rating	1000 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Black
-------	-------



Descriptions

Description	#14-2/0 AWG GEL TAP SPLICE KIT (W/CONNECTOR)
extra long description	NSI ESGTS-2/0 Easy-Splice UF Kit
Features	Easy-Splice Gel Tap Splice Kit with Connector for #14 - 2/0 AWG The Easy-Splice gel tap splice kit provides a fast and simple method for connecting, insulating, and environmentally sealing low-voltage splices. The splice kit is designed for underground and overhead environments and is useful for street lighting applications. The splice kit's dual-rated mechanical connector splices a wide range of cables, including copper and aluminum. The connector's four port design allows maximum inventory flexibility. T
Long Description	Easy-Splice Gel Tap Splice Kit with Connector for #14 - 2/0 AWG The Easy-Splice gel tap splice kit provides a fast and simple method for connecting, insulating, and environmentally sealing low-voltage splices. The splice kit is designed for underground and overhead environments and is useful for street lighting applications. The splice kit's dual-rated mechanical connector splices a wide range of cables, including copper and aluminum. The connector's four port design allows maximum inventory flexibility. T
Product Type	Easy-Splice Uf Kit
Special Features	Four Port Design With Dual Rated Mecahnical Connector

Manufacturer Information

Brand	NSI
GTIN	00662381168641
Manufacturers Part Number	ESGTS-2/0
UPC	662381168641

Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Gel Tap Splice Kits With Connector

Packaging

Carton	3
Weight Per each	0.26

Uses, Certifications, and Standards

Application	Splicing Wire
Operating Temperature	-40 C To 90 C
standard	ANSI C119.1-1986 Qualified