

DESCRIPTION

Metal Baffle trim in the 6" All-Pro trim family for use in Halo and All-Pro recessed downlighting.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Uses coil spring retention. High gloss white trim finish provides for easy cleaning and maintenance. Two plastic trim rings provided, narrow and wide, with metal baffle. Baffle available in black and white.

Lamp Listings - Incandescent

EI700	50W PAR30, 65W BR30, 75W R30, 75W PAR30L
EI700AT	
EI700R	
EI700RAT	

EI700U	65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 90W PAR38, 90W BR40, 100W R40
EI700UAT	

ET2700U	65W BR30, 75W R30, 75W PAR30, 75W PAR30L
ET2700UAT	


Lamp Listings - Incandescent

ET700	65W BR30, 75W R30, 75W PAR30
ET700R	65W BR30, 75W R30, 75W PAR30, 75W PAR30L

EI2700	50W PAR30, 65W BR30, 75W PAR30L
EI2700AT	
EI2700R	65W BR30, 75W PAR30L

Lamp Listings - GU24

H724ICAT	CF15/R30/GU24
H724ICATL	
H724RICAT	CF13/GU24 (spiral)
H724RICATL	



Height: 2-7/8" [73mm]
 Outside Diameter (wide): 7-1/4" [184mm]
 Outside Diameter (narrow): 8" [203mm]
 Narrow and Wide, Supplied with Trim

ORDERING INFORMATION


Trim

--

ERT707WHT = 6" Gloss white trim, white metal baffle
ERT707 = 6" Gloss white trim, black metal baffle



ERT707WHT
 Gloss White Trim,
 White Metal Baffle



ERT707
 Gloss White Trim,
 Black Metal Baffle

ERT707

6-Inch Metal Baffle

DESCRIPTION

Metal Baffle trim in the 6" All-Pro trim family for use in Halo and All-Pro recessed downlighting.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Uses coil spring retention. High gloss white trim finish provides for easy cleaning and maintenance. Two plastic trim rings provided, narrow and wide, with metal baffle. Baffle available in black and white.

Lamp Listings - Incandescent

EI700	50W PAR30, 65W BR30, 75W R30, 75W PAR30L
EI700AT	
EI700R	
EI700RAT	

EI700U	65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 90W PAR38, 90W BR40, 100W R40
EI700UAT	

ET2700U	65W BR30, 75W R30, 75W PAR30, 75W PAR30L
ET2700UAT	


Lamp Listings - Incandescent

ET700	65W BR30, 75W R30, 75W PAR30
ET700R	65W BR30, 75W R30, 75W PAR30, 75W PAR30L

EI2700	50W PAR30, 65W BR30, 75W PAR30L
EI2700AT	
EI2700R	65W BR30, 75W PAR30L

Lamp Listings - GU24

H724ICAT	CF15/R30/GU24
H724ICATL	
H724RICAT	CF13/GU24 (spiral)
H724RICATL	



Height: 2-7/8" [73mm]
 Outside Diameter (wide): 7-1/4" [184mm]
 Outside Diameter (narrow): 8" [203mm]
 Narrow and Wide, Supplied with Trim

ORDERING INFORMATION

Trim

--

ERT707WHT = 6" Gloss white trim, white metal baffle
ERT707 = 6" Gloss white trim, black metal baffle



ERT707WHT
 Gloss White Trim,
 White Metal Baffle



ERT707
 Gloss White Trim,
 Black Metal Baffle

ERT707

6-Inch Metal Baffle