


## ERT713

### Black Metal Baffle




- Socket supporting trim
- ERT713 - Friction clip retention
- ERT713TS - Torsion spring retention

EI700	40W A19, 65W BR30, 75W PAR30, 75W PAR30L, 90W BR40
EI700AT	
EI700R	
EI700RAT	
EI700NB	40W A19, 65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 90W BR40
EI700ATNB	



Height: 5" [127mm]  
OD: 7-1/4" [184mm]



**ERT713TS**  
High Gloss Appliance White Trim  
with Black Baffle and Torsion  
Spring Construction

**ERT713**  
High Gloss Appliance White Trim  
with Black Baffle

ET700	75W PAR30L, 85W BR30, 100W R30, 100W A19, 120W BR40
ET700R	65W BR30, 75W PAR30L

EI700U	60W A19, 75W PAR30, 75W PAR30L, 85W BR30, 120W BR40
EI700UAT	


## ERT713WHT

### White Metal Baffle



- Socket supporting trim
- ERT713WHT - Friction clip retention
- ERT713WHTTS - Torsion spring retention

EI700	40W A19, 65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 90W BR40
EI700AT	
EI700R	
EI700RAT	
EI700NB	
EI700ATNB	



Height: 5-3/8" [136mm]  
OD: 7-1/4" [184mm]



**ERT713WHTTS**  
High Gloss Appliance White Trim  
with White Baffle and Torsion  
Spring Construction

**ERT713WHT**  
High Gloss Appliance White Trim  
with White Baffle

ET700	75W PAR30L, 85W BR30, 100W R30, 100W A19, 120W BR40
ET700R	65W BR30, 75W PAR30L

EI700U	60W A19, 75W PAR30, 75W PAR30L, 85W BR30, 100W R30, 120W BR40
EI700UAT	


## ERT713L

### Black Metal Baffle



- Provides deeper lamp regression
- Socket supporting trim
- ERT713L - Friction clip retention
- ERT713LTS - Torsion spring retention

EI700	75W BR40, 65W BR30, 75W PAR30L
EI700AT	
EI700R	
EI700RAT	
EI700NB	
EI700ATNB	



Height: 5-3/8" [136mm]  
OD: 7-1/4" [184mm]



**ERT713LTS**  
High Gloss Appliance White Trim  
with Black Baffle and Torsion  
Spring Construction

**ERT713L**  
High Gloss Appliance White Trim  
with Black Baffle

ET700	75W A19, 75W PAR30L, 75W PAR30, 85W BR30, 100W R30, 120W BR40, 150W R40
ET700R	65W BR30, 75W PAR30L, 150W R40

EI700U	40W A19, 75W PAR30, 75W PAR30L, 85W BR30, 120W BR40
EI700UAT	

ADV111764

September 22, 2011 4:22 PM

Note: Specifications and Dimensions subject to change without notice.

Visit our web site at [www.cooperlighting.com](http://www.cooperlighting.com)