



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **F032V41ECO 32W T8 48" 4100K 90 Cri** *Sylvania-Ledvance*

|                  |                                                                                                                                                                                                                                                                                             |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | F032V41ECO                                                                                                                                                                                                                                                                                  |
| Manufacturer     | Sylvania-Ledvance                                                                                                                                                                                                                                                                           |
| Description      | 32W, 48 Inch Mol, T8 Octron Vivid Value Fluorescent Lamp<br>Combines Vivid Color Rendering With Entry Level Value, 4100K<br>Color Temperature, Rare Earth Phosphor, 90 Cri, Suitable For Is<br>or PRS Operation, Ecologic . Vivid Color: High Cri Lamps For Color<br>Critical Applications. |
| Weight per unit  | 0.4207 (lbs/each)                                                                                                                                                                                                                                                                           |
| Product Category | Linear Fluorescent Straight La                                                                                                                                                                                                                                                              |

### Features

|           |                       |
|-----------|-----------------------|
| Base      | Medium Bipin          |
| Lamp Type | RAPID & INSTANT START |
| lumens    | 2450                  |
| Shape     | T8                    |

### Material, Color, and Finish

|                             |    |
|-----------------------------|----|
| color rendering index (cri) | 90 |
|-----------------------------|----|

### Descriptions

|                        |                                                                                                                                                                                                                                                                                             |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | 32W T8 48" 4100K 90 CRI                                                                                                                                                                                                                                                                     |
| extra long description | SYL FO32V41ECO/22438 FO32V41ECO 30/                                                                                                                                                                                                                                                         |
| Long Description       | 32W, 48 inch MOL, T8 OCTRON VIVID VALUE fluorescent lamp<br>combines VIVID color rendering with entry level VALUE, 4100K<br>color temperature, rare earth phosphor, 90 CRI, suitable for IS or<br>PRS operation, ECOLOGIC . VIVID Color: High CRI lamps for color<br>critical applications. |

### Manufacturer Information

|                           |                     |
|---------------------------|---------------------|
| Brand                     | OSRAM SYLVANIA INC. |
| GTIN                      | 00046135224386      |
| Manufacturers Part Number | FO32/V41/ECO/22438  |
| UPC                       | 046135224386        |

### Taxonomies, Classifications, and Categories

|                      |             |
|----------------------|-------------|
| Category Description | Fluorescent |
| Type                 | FLUORESCENT |

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 30     |
| Weight Per each | 0.4207 |