
THREE BAY MODULE MOUNTING BRACKET

F7510 | [On-Q](#)



FEATURES & BENEFITS

Want to increase the capacity of your On-Q enclosure? No problem. Innovative integration brackets allow you to mix and match products for seamless connectivity. This means that you can stick with what you're familiar with - your favorite products will be right there just the way you like them. Imagine the possibilities.



Allows mounting of 3 single size modules.
Mounts vertically or horizontally for maximum flexibility.
Additional brackets can be added for expansion.

SPECIFICATIONS

GENERAL INFO

Color: White
Finish: Reflective Powder Coat
Type: Bracket

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Yes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
UL Listing No: ANSI/UL 1863
UL Standard: Yes
UN SPSC: 43223306

DIMENSIONS

Depth (Metric): 4.13 cm
Depth (US): 1.625"

Height (Metric): 8.54 cm
Height (US): 3.36"
Width (Metric): 34.53 cm
Width (US): 13.6 in
Thickness (US): 18 Gauge

TECHNICAL INFORMATION

Material: Cold Rolled Steel
Mounting: Enclosure

THREE BAY MODULE MOUNTING BRACKET

F7510 | [On-Q](#)



FEATURES & BENEFITS

Want to increase the capacity of your On-Q enclosure? No problem. Innovative integration brackets allow you to mix and match products for seamless connectivity. This means that you can stick with what you're familiar with - your favorite products will be right there just the way you like them. Imagine the possibilities.



Allows mounting of 3 single size modules.
Mounts vertically or horizontally for maximum flexibility.
Additional brackets can be added for expansion.

SPECIFICATIONS

GENERAL INFO

Color: White
Finish: Reflective Powder Coat
Type: Bracket

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Yes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
UL Listing No: ANSI/UL 1863
UL Standard: Yes
UN SPSC: 43223306

DIMENSIONS

Depth (Metric): 4.13 cm
Depth (US): 1.625"

Height (Metric): 8.54 cm
Height (US): 3.36"
Width (Metric): 34.53 cm
Width (US): 13.6 in
Thickness (US): 18 Gauge

TECHNICAL INFORMATION

Material: Cold Rolled Steel
Mounting: Enclosure