



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F66G24 6X6X24 N1 HC STRT SCT

Hoffman Enclosures, Inc.

| | |
|------------------|--|
| Catalog Number | F66G24 |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Lay-In Wireway, Gray, Polyester Powder Paint, Steel, Hinged Cover, 6 In Overall Height, 24 In Overall Length, 6 In Overall Width, 43.52 LB |
| Weight per unit | 43.5 (lbs/each) |
| Product Category | Nema Type 1 Wireway & Fittings |

Features

| | |
|-----------|-------|
| ip rating | IP30 |
| Knockouts | FALSE |

Material, Color, and Finish

| | |
|------------|----------------------------|
| Color Code | ANSI 61 |
| Style | Liftoff Cover no Knockouts |

Dimensions and Weight

| | |
|--------|---|
| Height | 6 |
| Width | 6 |

Descriptions

| | |
|------------------------|--|
| Description | 6X6X24 N1 HC STRT SCT |
| extra long description | NVENT HOF F66G24 Strt Sect LI HC Tp |
| Features | Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sections are available in lengths from 12 inch to 120 inch, with or without knockouts. |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510523503 |
| UPC | 783510523503 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type | Commercial Lay-in Hinged-Cover Type 1 Wireway;Straight Section |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 4 |
| Weight Per each | 43.52 |

Uses, Certifications, and Standards

| | |
|-------------|--------------------|
| Application | Power Distribution |
| nema rating | 1 |