

Eaton FAZ-C50{3-NA

Catalog Number: FAZ-C50/3-NA

Eaton FAZ branch protector,UL 489 Industrial miniature circuit breaker - supplementary protector,Medium levels of inrush current are expected,50 A,10 kAIC,Three-pole,240 V,5-10X /n,50-60 Hz,Screw terminals,C Curve

General specifications



Photo is representative

Product Name

Eaton FAZ branch protector

Catalog Number

FAZ-C50/3-NA

UPC

786689240813

Product Length/Depth

2.1 in

Product Height

3 in

Product Width

4.1 in

Product Weight

0.75 lb

Warranty

1 year

Certifications

UL 489

Physical Attributes

Number of poles

Three-pole

Terminals

Screw

Type

UL 489 Industrial miniature circuit breaker - supplementary protector

Performance Ratings

Amperage Rating

50 A

Circuit protection

C curve

Frequency rating

50-60 Hz

Interrupt rating

10 kAIC

Trip Type

5-10X /n

Voltage rating

277/480V

Miscellaneous

Application

Suitable for applications where medium levels of inrush current are expected

Resources

Catalogs

[UL 489 DIN rail miniature circuit breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - FAZ-C50/3-NA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton FAZ-C50{3-NA

Catalog Number: FAZ-C50/3-NA

Eaton FAZ branch protector,UL 489 Industrial miniature circuit breaker - supplementary protector,Medium levels of inrush current are expected,50 A,10 kAIC,Three-pole,240 V,5-10X /n,50-60 Hz,Screw terminals,C Curve

General specifications



Photo is representative

Product Name

Eaton FAZ branch protector

Catalog Number

FAZ-C50/3-NA

UPC

786689240813

Product Length/Depth

2.1 in

Product Height

3 in

Product Width

4.1 in

Product Weight

0.75 lb

Warranty

1 year

Certifications

UL 489

Physical Attributes

Number of poles

Three-pole

Terminals

Screw

Type

UL 489 Industrial miniature circuit breaker - supplementary protector

Performance Ratings

Amperage Rating

50 A

Circuit protection

C curve

Frequency rating

50-60 Hz

Interrupt rating

10 kAIC

Trip Type

5-10X /n

Voltage rating

277/480V

Miscellaneous

Application

Suitable for applications where medium levels of inrush current are expected

Resources

Catalogs

[UL 489 DIN rail miniature circuit breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - FAZ-C50/3-NA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia