



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1725 East Highway 82
76240-0000, TX Gainesville
Phone: 940-612-1388
Fax: 940-612-1499



FF2H 2HR SPST Wall Timer

Intermatic Inc.

Catalog Number	FF2H
Manufacturer	Intermatic Inc.
Description	Spring Wound Countdown Timer, Commercial, 125-277 Vac, 50/60 Hz, SPST, 2 Hour Max, Without Hold, Silver
Weight per unit	0.3830 (lbs/each)
Product Category	Electromechanical Time Switches

Features

action	1 x SPST
amperage rating	15
connection	Teeter Type
Contact Configuration	1 NO
Contact Rating	7 AMP @ 125 VAC (Tungsten), 20 AMP @ 125 VAC (Resistive), 10 AMP @ 250/277 VAC (Resistive)
motor power	1 HP @ 120 VAC, 2 HP @ 240 VAC
Poles	1
Timing Range	2
Voltage Rating	125 - 277

Dimensions and Weight

Size	2.79 HEIGHT X 1.6 WIDTH X 1.19 DEPTH IN, 70.86 HEIGHT X 40.64 WIDTH X 30.22 DEPTH MM
------	--



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1725 East Highway 82
76240-0000, TX Gainesville
Phone: 940-612-1388
Fax: 940-612-1499

Descriptions

Description	2HR SPST WALL TIMER
extra long description	INT-MAT FF2H Spring Wound Countdown
Features	The FF Series Commercial Countdown Timers are designed to replace any standard wall switch and do not require electricity to operate. These energy-efficient switches automatically limit the ON times for fans, lighting, motors, heaters, and other energy consuming loads. A commercial "brushed metal" look plate (plastic construction) meets NEC requirements. *NOTE: Not for use with sunlamps, saunas, or loads that could cause personal injury if timed incorrectly.
Long Description	Spring Wound Countdown Timer, Commercial, 125-277 VAC, 50/60 Hz, SPST, 2 Hour Max, Without Hold, Silver
Product Type	Spring Wound Countdown Timer, Commercial, 125-277 Vac, 50/60
Special Features	Features: Energy-Efficient Mechanical Timers do not require Electricity to Operate, Automatically Limit the ON Times, Rugged Time Dial Plate Easily withstands the Abuse Encountered in Commercial Environments, Commercial "Brushed Metal" (Plastic Construction) look meets NEC Requirements, Press-On Knob Design Ensures Quick and Easy Installation, CFL Compatible, Provide Direct Replacement of a Standard Wall Switch in a Single Gang 2-1/2 IN Deep Junction Boxes, Spiral Time Scale to Provide Easy Selection of th

Manufacturer Information

Brand	Intermatic
GTIN	00078275074002
Manufacturers Part Number	FF2H
UPC	078275074002

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Commercial Spring Wound Auto-Off

Packaging

Carton	1
Package	6
Weight Per each	0.383



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1725 East Highway 82
76240-0000, TX Gainesville
Phone: 940-612-1388
Fax: 940-612-1499

Uses, Certifications, and Standards

Application	Indoor, CFLs Lighting, Fans, Electric Motors, Heaters, HVACR
Frequency Rating	50/60
Mounting	WALL MOUNT
standard	cCSAus Certified, UL Listed, UL Recognized, HVACR, NEC