


NEW!
more on
reverse

Floor Box for New Concrete

Non-Metallic Box with SIX Conduit Hubs • Reversible Leveling Ring

SIDE A

Fits 6" round covers with a 3-1/2" screw hole pattern




SIDE B

Fits 6" round covers with a 3-3/8" screw hole pattern



THREE options for low voltage divider positioning



Arlington's FLOOR BOXES, COVER KITS, and accessories **FOR NEW CONCRETE** are the low cost, *convenient* way to install a receptacle *flush with a new floor*.

Made of heavy-duty plastic, our NEW FLBC4502 4.5" non-metallic **concrete floor box** has more! – SIX conduit hubs and FOUR plugs. And THREE options for positioning the low voltage divider in the box.

The NEW FLBC4502LR **leveling ring** makes installing a cover easy on ANY 4.5" concrete box including our FLBC4500 and the new FLBC4502. **It's REVERSIBLE!** Side A fits any 6" round cover with a 3-1/2" screw hole pattern. Side B has a second set of holes that fits 6" covers with a 3-3/8" screw hole pattern.



Arlington offers a variety of **cover kits** to fit our concrete boxes – Round with flip lids or threaded plugs in brass or nickel-plated brass. Metal trapdoor covers with three device options. And in plastic, in six colors.

Get a great-looking, time-saving receptacle installation in new concrete with floor box kits, covers and more - from Arlington!

ARLINGTON COVER KITS for FLBC4502 and FLBC4500




A 
Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Concrete Floor Boxes, Cover Kits, Accessories


Put a Receptacle in New Concrete – The Easy, Low Cost Way!



CATALOG NUMBER	UPC/DCI/NAED MFG. #018997	CONCRETE FLOOR BOXES & LEVELING RINGS DESCRIPTION	UNIT PKG	STD PKG
FLBC4502	34004	4.5" Non-metallic ROUND BOX WITH (6) CONDUIT HUBS for New Concrete Pours. UL Listed. Includes divider, pour cap, (4) 3/4" plugs and (2) 1" plugs for unused hubs.	1	5
FLBC4502LR	34005	REVERSIBLE LEVELING RING for Arlington FLBC4502, FLBC4500 and others' 4.5" boxes and 6" covers	1	10
FLBC4500	22010	4.5" Non-metallic ROUND BOX WITH (4) CONDUIT HUBS for New Concrete Pours. UL Listed. Includes divider, pour cap, (2) 3/4" plugs and (1) 1" plug for unused hubs.	1	5
FLBC4500LR	22011	LEVELING RING for Arlington FLBC4502, FLBC4500 and others' 4.5" boxes and 6" covers	1	10
FLBC4500LRBE	20745	LEVELING RING/BOX EXTENDER Extends installed boxes up to 2". For Arlington FLBC4502, FLBC4500 and others' 4.5" boxes and 6" covers.	1	10

EASY TO INSTALL CONCRETE BOXES

- 1 Set concrete floor box into position. Secure in place through molded mounting ears. Option: Use 1/4-20 screws to level/position the box.
- 2 Install conduit as needed using PVC cement. Pull wires through conduit as required.
- 3 Install plugs (provided) w/ PVC cement to seal unused openings.
- 4 Install pour cap. Pour concrete to finished depth.
- 5 After concrete has cured, remove pour cap. Use a saw to cut box to finished floor height.



Complete the installation with a leveling ring and one of these cover trim kits.



CATALOG NUMBER	UPC/DCI/NAED MFG. #018997	DESCRIPTION FINISH/COLOR, COVER STYLE	NOTES	UNIT PKG	STD PKG
FLB6230MBLR	34008	COVER KIT 6" Round, Brass w (2) flip lids	* hole pattern fits leveling ring	1	10
FLB6230NLLR	34009	COVER KIT 6" Round, Nickel-plated w (2) flip lids	* hole pattern fits leveling ring	1	10
FLB6220MBLR	22959	COVER KIT 6" Round, Brass w (2) threaded plugs	* hole pattern fits leveling ring	1	10
FLB6220NLLR	22960	COVER KIT 6" Round, Nickel-plated w (2) threaded plugs	* hole pattern fits leveling ring	1	10

Metal Cover Kits also available without the Leveling Ring. Delete suffix 'LR'.

PLASTIC COVER KITS

FLBC4520LA	09674	COVER KIT 6" Round, Light Almond – Plastic gasketed cover, mounting plate, leveling ring	1	10
FLBC4520W	13838	COVER KIT 6" Round, White – Plastic gasketed cover, mounting plate, leveling ring	1	10
FLBC4520GY	09673	COVER KIT 6" Round, Gray – Plastic gasketed cover, mounting plate, leveling ring	1	10
FLBC4520BR	09672	COVER KIT 6" Round, Brown – Plastic gasketed cover, mounting plate, leveling ring	1	10
FLBC4520CA	09669	COVER KIT 6" Round, Caramel – Plastic gasketed cover, mounting plate, leveling ring	1	10
FLBC4520BL	09671	COVER KIT 6" Round, Black– Plastic gasketed cover, mounting plate, leveling ring	1	10

TRAPDOOR STYLE, METAL COVERS

FLBT6620UMB	22047	Trapdoor Cover Round, Brass. Tamper-resistant 20A receptacle with (2) USB ports	1	10
FLBT6620MB	22052	Trapdoor Cover Round, Brass. Tamper-resistant 20A receptacle	1	10
FLBT6620GMB	22053	Trapdoor Cover Round, Brass. Tamper-resistant GFCI 20A receptacle	1	10
FLBT6620UNL	22048	Trapdoor Cover Round, Nickel-plated. Tamper-resistant 20A receptacle with (2) USB ports	1	10
FLBT6620NL	22054	Trapdoor Cover Round, Nickel-plated. Tamper-resistant 20A receptacle	1	10
FLBT6620GNL	22055	Trapdoor Cover Round, Nickel-plated. Tamper-resistant GFCI 20A receptacle	1	10

Trapdoor cover kits also available with 15A receptacles. See FLBT6615 series on our website.



FLBT6620UMB

FLBT6620NL

FLBT6620GMB

Distributed by

Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com


NEW!
more on
reverse

Floor Box for New Concrete

Non-Metallic Box with SIX Conduit Hubs • Reversible Leveling Ring

SIDE A

Fits 6" round covers with a 3-1/2" screw hole pattern




SIDE B

Fits 6" round covers with a 3-3/8" screw hole pattern

NEW!
REVERSIBLE
Leveling Ring



THREE options
for low voltage
divider positioning



Arlington's FLOOR BOXES, COVER KITS, and accessories **FOR NEW CONCRETE** are the low cost, *convenient* way to install a receptacle *flush with a new floor*.

Made of heavy-duty plastic, our **NEW FLBC4502 4.5" non-metallic concrete floor box** has more! – **SIX** conduit hubs and **FOUR** plugs. And **THREE** options for positioning the low voltage divider in the box.

The **NEW FLBC4502LR leveling ring** makes installing a cover easy on *ANY 4.5" concrete box* including our FLBC4500 and the new FLBC4502. **It's REVERSIBLE!** *Side A* fits any 6" round cover with a 3-1/2" screw hole pattern. *Side B* has a second set of holes that fits 6" covers with a 3-3/8" screw hole pattern.



Arlington offers a variety of **cover kits** to fit our concrete boxes – Round with flip lids or threaded plugs in brass or nickel-plated brass. Metal trapdoor covers with three device options. And in *plastic*, in *six colors*.

Get a great-looking, time-saving receptacle installation *in new concrete* with floor box kits, covers and more - from Arlington!

ARLINGTON COVER KITS for FLBC4502 and FLBC4500



FLB6230MBLR KIT
METAL COVER, FLIP LIDS
& LEVELING RING



FLB6220NL KIT
METAL COVER, THREADED PLUGS



FLB4520 SERIES KITS
PLASTIC COVERS
IN 6 COLORS




FLBT6620 SERIES
TRAPDOOR COVERS

A 
Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Concrete Floor Boxes, Cover Kits, Accessories


Put a Receptacle in New Concrete – The Easy, Low Cost Way!



CATALOG NUMBER	UPC/DCI/NAED MFG. #018997	CONCRETE FLOOR BOXES & LEVELING RINGS DESCRIPTION	UNIT PKG	STD PKG
FLBC4502	34004	4.5" Non-metallic ROUND BOX WITH (6) CONDUIT HUBS for New Concrete Pours. UL Listed. Includes divider, pour cap, (4) 3/4" plugs and (2) 1" plugs for unused hubs.	1	5
FLBC4502LR	34005	REVERSIBLE LEVELING RING for Arlington FLBC4502, FLBC4500 and others' 4.5" boxes and 6" covers	1	10
FLBC4500	22010	4.5" Non-metallic ROUND BOX WITH (4) CONDUIT HUBS for New Concrete Pours. UL Listed. Includes divider, pour cap, (2) 3/4" plugs and (1) 1" plug for unused hubs.	1	5
FLBC4500LR	22011	LEVELING RING for Arlington FLBC4502, FLBC4500 and others' 4.5" boxes and 6" covers	1	10
FLBC4500LRBE	20745	LEVELING RING/BOX EXTENDER Extends installed boxes up to 2". For Arlington FLBC4502, FLBC4500 and others' 4.5" boxes and 6" covers.	1	10

EASY TO INSTALL CONCRETE BOXES

- 1 Set concrete floor box into position. Secure in place through molded mounting ears. Option: Use 1/4-20 screws to level/position the box.
- 2 Install conduit as needed using PVC cement. Pull wires through conduit as required.
- 3 Install plugs (provided) w/ PVC cement to seal unused openings.
- 4 Install pour cap. Pour concrete to finished depth.
- 5 After concrete has cured, remove pour cap. Use a saw to cut box to finished floor height.



Complete the installation with a leveling ring and one of these cover trim kits.



CATALOG NUMBER	UPC/DCI/NAED MFG. #018997	DESCRIPTION FINISH/COLOR, COVER STYLE	NOTES	UNIT PKG	STD PKG
FLB6230MBLR	34008	COVER KIT 6" Round, Brass w (2) flip lids	* hole pattern fits leveling ring	1	10
FLB6230NLLR	34009	COVER KIT 6" Round, Nickel-plated w (2) flip lids	* hole pattern fits leveling ring	1	10
FLB6220MBLR	22959	COVER KIT 6" Round, Brass w (2) threaded plugs	* hole pattern fits leveling ring	1	10
FLB6220NLLR	22960	COVER KIT 6" Round, Nickel-plated w (2) threaded plugs	* hole pattern fits leveling ring	1	10

Metal Cover Kits also available without the Leveling Ring. Delete suffix 'LR'.

PLASTIC COVER KITS

FLBC4520LA	09674	COVER KIT 6" Round, Light Almond – Plastic gasketed cover, mounting plate, leveling ring	1	10
FLBC4520W	13838	COVER KIT 6" Round, White – Plastic gasketed cover, mounting plate, leveling ring	1	10
FLBC4520GY	09673	COVER KIT 6" Round, Gray – Plastic gasketed cover, mounting plate, leveling ring	1	10
FLBC4520BR	09672	COVER KIT 6" Round, Brown – Plastic gasketed cover, mounting plate, leveling ring	1	10
FLBC4520CA	09669	COVER KIT 6" Round, Caramel – Plastic gasketed cover, mounting plate, leveling ring	1	10
FLBC4520BL	09671	COVER KIT 6" Round, Black– Plastic gasketed cover, mounting plate, leveling ring	1	10

TRAPDOOR STYLE, METAL COVERS

FLBT6620UMB	22047	Trapdoor Cover Round, Brass. Tamper-resistant 20A receptacle with (2) USB ports	1	10
FLBT6620MB	22052	Trapdoor Cover Round, Brass. Tamper-resistant 20A receptacle	1	10
FLBT6620GMB	22053	Trapdoor Cover Round, Brass. Tamper-resistant GFCI 20A receptacle	1	10
FLBT6620UNL	22048	Trapdoor Cover Round, Nickel-plated. Tamper-resistant 20A receptacle with (2) USB ports	1	10
FLBT6620NL	22054	Trapdoor Cover Round, Nickel-plated. Tamper-resistant 20A receptacle	1	10
FLBT6620GNL	22055	Trapdoor Cover Round, Nickel-plated. Tamper-resistant GFCI 20A receptacle	1	10

Trapdoor cover kits also available with 15A receptacles. See FLBT6615 series on our website.



FLBT6620UMB

FLBT6620NL

FLBT6620GMB

Distributed by

Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com