



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1701 North Jackson Suite E  
78501-0000, TX McAllen  
Phone: 956-331-2410  
Fax: 956-331-2411



## FMLWL24840 2' Led Wrap 40K 1200LM

*Lithonia Lighting - Acuity*

Catalog Number	FMLWL24840
Manufacturer	Lithonia Lighting - Acuity
Description	The Low-Profile 2-FT. Long FMLWL Led Wraparound By Lithonia Lighting® Provides Efficient and Economical Ambient Lighting In Surface-Mount Applications With Full Dimensions Of 24.5-In X 5.5-In X 2.6-In. It Is Ideal For Many Applications Including Corridors, Kitchens, Breakrooms, Utility Work Areas and Stairways.
Weight per unit	2.4 (lbs/each)
Product Category	Led Surface Architectural & SP

### Features

average life	50,000
dimensions	24.5 x 5.5 x 2.6
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	1400 LM
Material	Steel
Maximum Operating Temperature	40
pallet quantity	224
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120
Warranty	5
Wattage	19.6

### Material, Color, and Finish

Color	White
color rendering index (cri)	85
color temperature	4000
Finish	Gloss
Style	CONTEMPORARY

### Dimensions and Weight

Height	2.58
Length	24.45
Width	5.48



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1701 North Jackson Suite E  
78501-0000, TX McAllen  
Phone: 956-331-2410  
Fax: 956-331-2411

## Descriptions

Description	2' LED WRAP 40K 1200LM
extra long description	LITH FMLWL 24 840 Wraparound, 2FT x
Features	Contractor Select
Long Description	The low-profile 2-ft. long FMLWL LED Wraparound by Lithonia Lighting® provides efficient and economical ambient lighting in surface-mount applications with full dimensions of 24.5-in x 5.5-in x 2.6-in. It is ideal for many applications including corridors, kitchens, breakrooms, utility work areas and stairways.
Product Type	Wraparound

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00888791197921
Manufacturers Part Number	FMLWL 24 840
UPC	888791197921

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Wraparound

## Trade Size

aperture size	2FT,4FT
---------------	---------

## Packaging

Carton	1
Weight	2.5
Weight Per each	2.4

## Uses, Certifications, and Standards

Application	Government,Hospitality,Offices & Banks,Residential,Utility, Closet
environmental conditions	Indoor
Mounting	SURFACE
standard	cUL,ULDL Standard