

# Eaton FMVA11LCY-UNV34-76

Catalog Number: FMVA11LCY-UNV34-76

Eaton Crouse-Hinds series Champ FMVA LED floodlight, Cool white, Dimmable driver, 3/4" entry, 320W equivalent, Heat and impact resistant glass lens, 11000 lumens, 144 lm/W, Die cast aluminum, Yoke mount, 347-480 Vac, 84W, 7x6 optics

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Champ FMVA LED floodlight	FMVA11LCY-UNV34-76
	<b>UPC</b>
	662276885172
<b>Product Length/Depth</b>	<b>Product Height</b>
15.5 in	12 in
<b>Product Width</b>	<b>Product Weight</b>
7 in	32.5 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

IEC

IECEX/ATEX

### NEC hazardous rating

Class I, Division 2

Class I, Zone 2

Class II, Division 1

Class III

### NEMA Rating

4X

### Ingress protection (IP) ratings

IP66

## Product specifications

### Lamp type

LED

### Lumens

11000

### Lumens per watt

144

### Color temperature

Cool white

### Mounting Method

Yoke

### Voltage rating

347-480 Vac

### Frequency rating

50/60 Hz

### Optical distribution

7x6

### Entry size

3/4"

### Lens material

Heat and impact resistant glass

### Wattage

84 W

### Dimming

Dimmable driver

### Equivalent luminaire

320W

### Power factor

> 0.90

### Material

Die cast aluminum

## Resources

[3D models](#)

SP3D Design Package - Champ FMVA LED Hazardous Area Floodlights

### Brochures

Crouse-Hinds series DLC approved lighting products

Crouse-Hinds series Champ FMVA LED Floodlights - 9,000 to 15,000 lumens brochure

### Catalogs

Crouse-Hinds series Champ FMVA LED Floodlights - 9,000 to 15,000 lumens catalog page

### Certification reports

Champ FMVA LED Hazardous Area Floodlights ABS certification

Champ FMVA LED Hazardous Area Floodlights UL certification

Champ FMVA LED Hazardous Area Floodlights ATEX Certificate

Champ FMVA LED Hazardous Area Floodlights Canadian certification

Champ FMVA LED Hazardous Area Floodlights IECEx Certificate of Conformity

Champ FMVA LED Hazardous Area Floodlights EC-Declaration of Conformity

### Installation instructions

IF 1889 - Champ FMVA/PFMA LED Floodlight Driver Replacement

IF 1883 - Champ FMVA LED Floodlight

### Specifications and datasheets

Eaton Specification Sheet - FMVA11LCY-UNV34-76



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia