

Eaton FMVA13LCY-UNV34-76

Catalog Number: FMVA13LCY-UNV34-76

Eaton Crouse-Hinds series Champ FMVA LED floodlight, Cool white, Dimmable driver, 3/4" entry, 400W equivalent, Heat and impact resistant glass lens, 13000 lumens, 143 lm/W, Die cast aluminum, Yoke mount, 347-480 Vac, 95W, 7x6 optics

General specifications

| | |
|---|--------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series Champ FMVA LED floodlight | FMVA13LCY-UNV34-76 |
| | UPC |
| | 662276885134 |
| Product Length/Depth | Product Height |
| 15.5 in | 12 in |
| Product Width | Product Weight |
| 7 in | 35.7 lb |

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

IEC

IECEX/ATEX

NEC hazardous rating

Class I, Division 2

Class I, Zone 2

Class II, Division 1

Class III

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lamp type

LED

Lumens

13000

Lumens per watt

143

Color temperature

Cool white

Mounting Method

Yoke

Voltage rating

347-480 Vac

Frequency rating

50/60 Hz

Optical distribution

7x6

Entry size

3/4"

Lens material

Heat and impact resistant glass

Wattage

95W

Dimming

Dimmable driver

Equivalent luminaire

400W

Power factor

> 0.90

Material

Die cast aluminum

Resources

[3D models](#)

SP3D Design Package - Champ FMVA LED Hazardous Area Floodlights

Brochures

Crouse-Hinds series DLC approved lighting products

Crouse-Hinds series Champ FMVA LED Floodlights - 9,000 to 15,000 lumens brochure

Catalogs

Crouse-Hinds series Champ FMVA LED Floodlights - 9,000 to 15,000 lumens catalog page

Certification reports

Champ FMVA LED Hazardous Area Floodlights ABS certification

Champ FMVA LED Hazardous Area Floodlights EC-Declaration of Conformity

Champ FMVA LED Hazardous Area Floodlights Canadian certification

Champ FMVA LED Hazardous Area Floodlights ATEX Certificate

Champ FMVA LED Hazardous Area Floodlights UL certification

Champ FMVA LED Hazardous Area Floodlights IECEx Certificate of Conformity

Installation instructions

IF 1883 - Champ FMVA LED Floodlight

IF 1889 - Champ FMVA/PFMA LED Floodlight Driver Replacement

Specifications and datasheets

Eaton Specification Sheet - FMVA13LCY-UNV34-76



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)