



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FNQR1410 Class CC Time Delay 1.4A Fuse

*Bussmann Fuses*

|                  |                                                                                                                                                               |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | FNQR1410                                                                                                                                                      |
| Manufacturer     | Bussmann Fuses                                                                                                                                                |
| Description      | Eaton Bussmann Series Class CC Fuse, FNQ, Time-Delay, Dual-Element Current Limiting Fuse, 1.4 A, Rejection Style Fuse, Interrupting Rating Of 200KA At 600vac |
| Weight per unit  | 0.1500 (lbs/each)                                                                                                                                             |
| Product Category | Small Dimension Fuses                                                                                                                                         |

### Features

|                  |                                   |
|------------------|-----------------------------------|
| amperage rating  | 1.40A                             |
| class            | Class CC                          |
| connection       | Ferrule End X Ferrule End         |
| dimensions       | 1.5000 IN X 0.4100 IN X 0.4100 IN |
| Fuse Class       | Class CC                          |
| interrupt rating | 200 kAIC                          |
| Material         | Melamine Tube                     |
| media            | Yes                               |
| Response Time    | 12 S at 200%                      |
| Voltage Rating   | 600 V                             |

### Dimensions and Weight

|      |                                     |
|------|-------------------------------------|
| Size | 13/32 In Diameter X 1-1/2 In Length |
|------|-------------------------------------|

### Descriptions

|                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| extra long description | BUSS FNQ-R-1-4/10 CLASS CC TIME DEL                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Features               | Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or |
| Long Description       | Eaton Bussmann Series Class CC fuse, FNQ, time-delay, dual-element current limiting fuse, 1.4 A, rejection style fuse, interrupting rating of 200kA at 600Vac                                                                                                                                                                                                                                                                                                                                                                   |
| Product Type           | Class CC Time Delay                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Special Features       | Rejection Style                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00051712496957 |
| Manufacturers Part Number | FNQ-R-1-4/10   |
| UPC                       | 051712496957   |

## Taxonomies, Classifications, and Categories

|                      |                           |
|----------------------|---------------------------|
| Category Description | GLASS FUSES (and ceramic) |
| Type                 | FUSE                      |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 10   |
| Weight Per each | 0.15 |

## Uses, Certifications, and Standards

|             |                                                                    |
|-------------|--------------------------------------------------------------------|
| Application | Ind Facilities & Factories - Facility: Safety and Security Systems |
| standard    | RoHS Compliant,CE Marked                                           |