



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street
38501-0000, TN Cookeville
Phone: 931-271-9933
Fax: 931-545-4298



FNQR25 25A 600V TD Class CC Fuse

Bussmann Fuses

Catalog Number	FNQR25
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Class CC Fuse, FNO, Time-Delay, Dual-Element Current Limiting Fuse, 25 A, Rejection Style Fuse, Interrupting Rating Of 200KA At 600vac
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	25
class	Class CC
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
Fuse Class	Class CC
interrupt rating	200 kAIC
Material	Melamine Tube
media	Yes
Response Time	12 S at 200%
Voltage Rating	600 V

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street
38501-0000, TN Cookeville
Phone: 931-271-9933
Fax: 931-545-4298

Descriptions

Description	25A 600V TD CLASS CC FUSE
extra long description	BUSS FNQ-R-25 CLASS CC TIME DELAY
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Long Description	Eaton Bussmann Series Class CC fuse, FNQ, time-delay, dual-element current limiting fuse, 25 A, rejection style fuse, interrupting rating of 200kA at 600Vac
Product Type	Class CC Time Delay
Special Features	Rejection Style

Manufacturer Information

Brand	Eaton
GTIN	00051712497138
Manufacturers Part Number	FNQ-R-25
UPC	051712497138

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

Packaging

Carton	10
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	CE Marked,RoHS Compliant